



**Electrical specifications**

**Center Frequency:** 2355 MHz  
**Bandwidth:** 10 MHz  
**Insertion Loss:** 1.0 dB Max  
**Passband Variation over Bandwidth:** 0.5 dB Max  
**Return Loss:** 20 dB Min  
**Group Delay Variation over Bandwidth:** 5ns Max  
**Rejection 1:** 13 dB @ 13 MHz offset from Fo  
**Rejection 2:** 20 dB @ 20 MHz offset from Fo  
**Power Handling:** 20 W Average, 150 W Peak


**Mechanical**

**Connector Type:** SMA (F)  
**Dimensions:** 170 x 140 x 54 mm

**Environmental**

**Operating Temperature:** 0 to +50° C

**Outline Drawing:**





**ANATECH ELECTRONICS INC**  
RF & Microwave Filters & Products

# 2350-2360 MHz Cavity Bandpass Filter

**Part Number: AB2355B992**



**Plot:**

