
Technical Data Sheet



COAXIAL TERMINATION N FEMALE 6 GHZ 200W



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.

Technical Data Sheet

COAXIAL TERMINATION N FEMALE 6 GHZ 200W



2/2			SERIES TERMINATION				R R404781020
			ELECT	RICAL CHA	RACTERISTIC	<u>:s</u>	
Frequency (GHz)		z)	DC - 3	3 - 6]		
V.S.W.R (≦)			1.20	1.40]		
Operating Frequency Range			e	DC - 6			GHz
Impedance DC Resistance				<u> </u>			Ω Ω ± 5%
Peak power at 25°C (1			%0)	2000			W
Average power at 25°C					200		W (Free Air Cooled)
							W (Conduction Cooled)
			MECH	ANICAL CHA	RACTERISTIC	<u>SS</u>	
	ectors		Ν		Female		MIL C39012
Weig	ht		1 896,0900 g				
			ENVIRO	MENTAL C		<u>rics</u>	
		Op	erating temperature	range		-55/+125 °C	
			prage temperature ra			-55/+125 °C	
				wer derating Ve	rsus temperature		
			100 90 80				
			Jan G Jan G Ja				
			-55		²⁵ 75 rature (°C)	125	
				SPECIFIC	ATION		
			<u>0</u> T	HER CHARA	CTERISTICS		
	Ν		WITH VERTICAL C	OOLING FIN	S AND NATUR		ΓΙΟΝ