






N ATTENUATOR 20 DB 3 GHZ 50W

PAGE 1/2 ISSUE 22-03-16B SERIES PART NUMBER R417020130

SCALE 1:2







All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
D 1	OTANU 500 OT551	PAGGWATER
Body	STAINLESS STEEL	PASSIVATED
Male center contact	BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL PHOSPHORUS 2
Female center contact	BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL PHOSPHORUS 2
Outer contact	-	-
Insulator	PTFE	
Gasket	SILICONE RUBBER	
Substrate	ALUMINA	
Resistor	THICK FILM	
Others parts	ALUMINIUM	BLACK PAINTING





Radiall 狐

PAGE 2/2 ISSUE 22-03-16B SERIES PART NUMBER R417020130

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 1	1 - 2	2 - 3
V.S.W.R (≤)	1.10	1.25	1.35
Deviation(±dB)	2.00	2.00	2.00

Operating Frequency Range	DC - 3	GHz	
Impedance	50	Ω	
Nominal Attenuation	20	dB	
Peak power at 25°C (1µs, 1‰)	5000	W	
Average power at 25°C		W (Free Air Cooled)	
	50	W (Conduction Cooled)	
For conduction cooling, a plate 500 cm2 x 3 mm(78 sq.in*1/8) min. is required			


MECHANICAL CHARACTERISTICS

Connectors	N	Male Female	MIL-C 39012
Weight	290,4100 g		

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55 /+125	°C
Storage temperature range	-55 /+125	°C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS