


NPN Silicon AF Transistors

- For AF driver and output stages
- High collector current
- Low collector-emitter saturation voltage
- Complementary types: BCX51...BCX53 (PNP)
- Pb-free (RoHS compliant) package¹⁾
- Qualified according AEC Q101



Type	Marking	Pin Configuration			Package
BCX54-16	BD	1=B	2=C	3=E	SOT89
BCX55	BE	1=B	2=C	3=E	SOT89
BCX55-16	BM	1=B	2=C	3=E	SOT89
BCX56	BH	1=B	2=C	3=E	SOT89
BCX56-10	BK	1=B	2=C	3=E	SOT89
BCX56-16	BL	1=B	2=C	3=E	SOT89

¹Pb-containing package may be available upon special request

Maximum Ratings

Parameter	Symbol	Value	Unit
Collector-emitter voltage BCX54	V_{CEO}	45	-
BCX55		60	
BCX56		80	
Collector-base voltage BCX54	V_{CBO}	45	V
BCX55		60	
BCX56		100	
Emitter-base voltage	V_{EBO}	5	
Collector current	I_C	1	A
Peak collector current, $t_p \leq 10$ ms	I_{CM}	1.5	
Base current	I_B	100	mA
Peak base current	I_{BM}	200	
Total power dissipation- $T_S \leq 120^\circ\text{C}$	P_{tot}	2	W
Junction temperature	T_j	150	$^\circ\text{C}$
Storage temperature	T_{stg}	-65 ... 150	

Thermal Resistance

Parameter	Symbol	Value	Unit
Junction - soldering point ¹⁾	R_{thJS}	≤ 15	K/W

¹For calculation of R_{thJA} please refer to Application Note Thermal Resistance

Electrical Characteristics at $T_A = 25^\circ\text{C}$, unless otherwise specified

Parameter	Symbol	Values			Unit
		min.	typ.	max.	
DC Characteristics					
Collector-emitter breakdown voltage $I_C = 10 \text{ mA}, I_B = 0$, BCX54	$V_{(\text{BR})\text{CEO}}$	45	-	-	V
$I_C = 10 \text{ mA}, I_B = 0$, BCX55		60	-	-	
$I_C = 10 \text{ mA}, I_B = 0$, BCX56		80	-	-	
Collector-base breakdown voltage $I_C = 100 \mu\text{A}, I_E = 0$, BCX54	$V_{(\text{BR})\text{CBO}}$	45	-	-	
$I_C = 100 \mu\text{A}, I_E = 0$, BCX55		60	-	-	
$I_C = 100 \mu\text{A}, I_E = 0$, BCX56		100	-	-	
Emitter-base breakdown voltage $I_E = 10 \mu\text{A}, I_C = 0$	$V_{(\text{BR})\text{EBO}}$	5	-	-	
Collector-base cutoff current $V_{CB} = 30 \text{ V}, I_E = 0$	I_{CBO}	-	-	0.1	μA
$V_{CB} = 30 \text{ V}, I_E = 0, T_A = 150^\circ\text{C}$		-	-	20	
DC current gain ¹⁾ $I_C = 5 \text{ mA}, V_{CE} = 2 \text{ V}$	h_{FE}	25	-	-	-
$I_C = 150 \text{ mA}, V_{CE} = 2 \text{ V}$, BCX55/BCX56		40	-	250	
$I_C = 150 \text{ mA}, V_{CE} = 2 \text{ V}$, BCX55-10/BCX56-10		63	100	160	
$I_C = 150 \text{ mA}, V_{CE} = 2 \text{ V}$, BCX54-16...BCX56-16		100	160	250	
$I_C = 500 \text{ mA}, V_{CE} = 2 \text{ V}$		25	-	-	
Collector-emitter saturation voltage ¹⁾ $I_C = 500 \text{ mA}, I_B = 50 \text{ mA}$	V_{CEsat}	-	-	0.5	V
Base-emitter voltage- $I_C = 500 \text{ mA}, V_{CE} = 2 \text{ V}$	$V_{\text{BE}(\text{ON})}$	-	-	1	


AC Characteristics

Transition frequency $I_C = 50 \text{ mA}, V_{CE} = 10 \text{ V}, f = 20 \text{ MHz}$	f_T	-	100	-	MHz
--	-------	---	-----	---	-----

¹⁾Pulse test: $t < 300 \mu\text{s}$; $D < 2\%$


DC current gain $h_{FE} = f(I_C)$

$V_{CE} = 2 \text{ V}$




Base-emitter saturation voltage

$I_C = f(V_{BEsat}), h_{FE} = 10$




Collector-emitter saturation voltage

$I_C = f(V_{CEsat}), h_{FE} = 10$




Collector current $I_C = f(V_{BE})$


$V_{CE} = 2 \text{ V}$




Collector cutoff current $I_{CBO} = f(T_A)$
 $V_{CBO} = 30 \text{ V}$




Total power dissipation $P_{tot} = f(T_S)$



Transition frequency $f_T = f(I_C)$
 V_{CE} = parameter in V, $f = 2 \text{ GHz}$




Permissible Pulse Load $R_{thJS} = f(t_p)$





Permissible Pulse Load

$$P_{\text{totmax}}/P_{\text{totDC}} = f(t_p)$$




Package Outline




1) Ejector pin markings possible

Foot Print




Marking Layout (Example)



Standard Packing

Reel ø180 mm = 1.000 Pieces/Reel
Reel ø330 mm = 4.000 Pieces/Reel



Edition 2006-02-01
Published by
Infineon Technologies AG
81726 München, Germany
© Infineon Technologies AG 2007.
All Rights Reserved.

Attention please!

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics ("Beschaffenheitsgarantie"). With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation warranties of non-infringement of intellectual property rights of any third party.

Information

For further information on technology, delivery terms and conditions and prices please contact your nearest Infineon Technologies Office (www.infineon.com).

Warnings

Due to technical requirements components may contain dangerous substances. For information on the types in question please contact your nearest Infineon Technologies Office.

Infineon Technologies Components may only be used in life-support devices or systems with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system, or to affect the safety or effectiveness of that device or system.

Life support devices or systems are intended to be implanted in the human body, or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.