


Photodiode 100 mm² with Integrated Thin Film Filter



FEATURES

- 100 mm² Square Active Area
- Responsivity @ 3 nm 0.16 A/W
- Detection Range 1 nm to 12 nm
- Shipped with Protective Cover

Electro-Optical Characteristics at 25°C

| Parameters | Test Conditions | Min | Тур | Max | Units |
|---|-----------------------|-----|------|-----|-------|
| Active Area | 10 mm x 10 mm | | 100 | | mm² |
| Responsivity | @ 3 nm | | 0.16 | | A/W |
| Shunt Resistance, Rsh | @ ±10 mV | 20 | | | Ohms |
| Reverse Breakdown Voltage, V _R | 1 _R = 1 μA | 5 | 10 | | Volts |
| Capacitance, C | $V_R = 0 V$ | | 10 | 44 | nF |


Thermal Parameters

| Storage and Operating Temperature Range | Units | | |
|---|--------------|--|--|
| Ambient | –10° to 40°C | | |
| Nitrogen or Vacuum | –20 to 80°C | | |
| Lead Soldering Temperature* | 260°C | | |


^{*0.080&}quot; from case for 10 seconds.

Revision November 26, 2019 Page 1 of 2

Typical Responsivity at 25°C



Package Information



Dimensions are in inch [metric] units.

Specifications are subject to change without prior notice.

Revision November 26, 2019 Page 2 of 2