



Summary

[Request a quote](#)

[Catalog](#)

Triax	1
Socket / Receptacle	Socket / Receptacle - Fixed Panel Front Mounted
Locking system	Push-pull
Jacket cable outside diameter [mm]	1.30 - 14.60 mm
Matching parts	FFA.1E.650.CLAC40
Series	E - Outdoor Stepped Insert

Technical details

Electrical Configuration

Triax	1
Contact Termination Triax	Solder
Insert configuration value	1E.650 - 1 Triax (50 Ohm)
Insulator	T: PTFE
Rated current	6 Amps
Impedance	50 Ohm
VSWR	1.01 + 0.17 * f/GHz
Vtest	1200 V (AC), 1690 V (DC)
Contact Type	Solder
Cable type	RGT 178, RGT 174, Belden 9222

https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/era-1e-650-ctl.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Form & Material

Shell style / Model id	ERA - Fixed receptacle, nut fixing
Socket / Receptacle	Fixed Panel Front Mounted
Housing material	Brass (chrome plated [SAE AMS 2460]) shell, collet nut and latch sleeve, nickel plated [SAE AMS QQ N 290] brass mid pieces
Locking system	Push-pull
Keying	Circular, female
Weight	19.91 g


Environment

Technical domain	Energy and Industrial, Test and Measurement
Environmental protection	IP68
Minimal temperature	-55°C / +200°C
Climatical Category	50/175/21
Humidity (max)	<=95% [at 60 deg C /140 F]
Shielding (min)	95 dB (10 MHz)
Shielding (min)	80 dB (1 GHz)
Shock Resistance	100 g [6 ms]
Vibration	15 g [10 Hz - 2000 Hz]
Salt Spray Corrosion	>1000 hr

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet
Jacket cable outside diameter [mm]	1.30 - 14.60 mm

Drawings



https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/era-1e-650-ctl.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Dimensions

	A	B	e	E	L	M	S1	S3	L1
mm.	20	21.5	M16x1.0	9	24	4.5	14.5	19	25.3
in.	0.79	0.85		0.35	0.94	0.18	0.57	0.75	1

https://www.lemo.com/int_en/solutions/originals/e-outdoor-stepped-insert/era-1e-650-ctl.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.