PRODUCT CODE: -

CATEGORY: -

B05 Package

Panel Mounting EMI / RFI Filter



Sr. No.	Parameter	Specification		
1	Product category / description	EMI/RFI Filter with single fuse & switch		
2	Mounting	Panel mounting		
3	Filter category	Single phase & single phase with surge suppressor		
	Electrical characteristics			
4	V/A rating	3 Amp, 6 Amp, 120/250VAC, 50/60Hz		
5	Insulation resistance at 500 VDC for 60 sec \pm 5 sec. (by shorting L & N terminals & w.r.t. earth)			
6	H.V.break down test for 60 sec ± 5 sec. (by shorting L & N terminals & w.r.t. earth)	2KVAC		
7	MTBF@40°c/230V(Mil-HB-217F)	1,650,000 hours		
	Operating / functional characteristics			
8	Operating temp. range	40°c/-25° +85°c		
9	Input terminals (standard)	IEC 60320 C14 inlet		
10	Output terminals (standard)	Fast on 6.3 x 0.8 mm / soldering lugs		
11	Size	(L-65 x W-50 x H-54.8) in mm.		
12	Material	CRCA 0.6 mm thickness		
13	Body	In fabricated CRCA metal can with nickel plating		
14	Current carrying parts	Cu alloy, tin/nickel plating		
	Reference standards			
15	Reference standard	EN60939-3:2015 & EN60939-2:2005, CSA C22.2 NO. 8-13, UL 1283 (7th Edition)		
	Safety approvals			
16	CE marking	Yes		
17	cCSAus	Yes		

						Elcom International Pvt. Ltd. 20, Prabhadevi Ind. Est., Mumbai - 400 025,
REV	IS	WAS	DATE	SIGN	APP.	India. Tel.: +91 22 66114444, Fax: +91 22 66114422, sales@elcom-in.com
Rev & Date: 00 & 28.11.18			11.18		www.elcom-in.com	
F: ENG-40.00					Copyright © 2018 by Elcom International Pvt.Ltd, India. All rights reserved	

The content of this document has been carefully checked and understood. However, Elcom not assume any liability whatsoever for any errors or inaccuracies of this document and the consequences thereof. Published specifications are subject to change without notice. Product suitability for any area of application must ultimately be determined by the customer.

ANNEXURE A

Standard variety						
Sr. No.	With reference to	Available option	RoHS / Non RoHS	Safety approvals & / or markings		
1	EMI/RFI Filter	Filter EMI/RFI single phase, 120/250 VAC, with/without surge suppressor, panel mounting with IEC 60320 C14 inlet with fuse & non illuminated red switch in fabricated metal can	RoHS COMPLIANT	c∰ _{us} (€		

Sr. No.	With reference to Product category	Available option	RoHS / Non RoHS	Safety approvals & / or markings	
		EMI/RFI Filter EMI/RFI Filter with surge suppressor EMI/RFI Filter for medical applications EMI/RFI Filter with surge suppressor for medical applications EMI/RFI Filter with special features	ROHS COMPLIANT	. ∰ _{us} C €	
2	Connection terminals	Input - IEC 60320 C14 inlet Output - Fast on 6.3 x 0.8 terminals /wire lead terminals	RoHS	c ∰ us (€	
3	Switch availability	Non illuminated switch (Red/Black/Green) Illuminated switch (Red/Amber/Green)	RoHS	c∰ us (€	
4	Flammability corresponding	UL 94 V-2 or better	RoHS COMPLIANT	c∰ us (€	
5	Operating voltage	Single phase 120 Vac Single Phase 250 Vac	RoHS	c∰ us (€	
6	Operating frequency	• 50/60Hz	RoHS COMPLIANT	c∰ us (€	
7	Design corresponding to	 EN60939-3:2015 & EN60939-2:2005 CSA C22.2 NO. 8-13 UL 1283 (7th Edition) 	RoHS	c∰ _{us} (€	
8	Mounting	Panel mounting	RoHS COMPLIANT		

						Elcom International Pvt. Ltd. 20, Prabhadevi Ind. Est., Mumbai - 400 025,
REV	IS	WAS	DATE	SIGN	APP.	India. Tel.: +91 22 66114444, Fax: +91 22 66114422, sales@elcom-in.com
Rev & Date: 00 & 28.11.18			11.18		www.elcom-in.com	
F: ENG-40.00						Copyright © 2018 by Elcom International Pvt.Ltd, India. All rights reserved

The content of this document has been carefully checked and understood. However, Elcom not assume any liability whatsoever for any errors or inaccuracies of this document and the consequences thereof. Published specifications are subject to change without notice. Product suitability for any area of application must ultimately be determined by the customer.