






N ATTENUATOR 10 DB 3 GHZ 50W

PAGE 1/2 ISSUE 11-03-16B SERIES PART NUMBER R417010110

SCALE 1:2







All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)	
Body	STAINLESS STEEL	PASSIVATED	
Male center contact Female center contact	BERYLLIUM COPPER BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL PHOSPHORUS 2 GOLD 0.5 OVER NICKEL PHOSPHORUS 2	
Outer contact	-	-	
Insulator	PTFE		
Gasket	SILICONE RUBBER		
Substrate	ALUMINA		
Resistor	THICK FILM		
Others parts	ALUMINIUM	BLACK PAINTING	





N ATTENUATOR 10 DB 3 GHZ 50W

PAGE 2/2	ISSUE 11-03-16B	SERIES ATTENUATOR	PART NUMBER R417010110
-----------------	------------------------	----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 1	1 - 2	2 - 3
V.S.W.R (≤)	1.10	1.25	1.35
Deviation(±dB)	0.70	0.70	0.70

Ω
dB
W
W (Free Air Cooled)
W (Conduction Cooled)


MECHANICAL CHARACTERISTICS

Connectors	N	Male Female	MIL-C 39012
Weight	431,8200 g		

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55 /+125	°C
Storage temperature range	-55 /+125	°C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS