Class G

Open fuse blocks





Catalog symbols:

- BG_ (1-30A)
- G_ (35-60A)

Description:

A range of open 1-, 2- and 3-pole fuse blocks for Class G fuses.

Specifications:

Ratings

- Volts:
 - 600V (1-20A)
 - 480V (25-60A)
- Amps: 1 to 60A
- Withstand rating: 100kA RMS Sym

Agency information

- 1-30A: UL® Recognized, UL 512, Guide IZLT2, File E14853
- 35-60A: UL Listed, UL 512, Guide IZLT, File E14853
- 1-60A cULus, C22.2 No. 39, Class 6225-01; File 47235
- RoHS compliant

Recommended fuses:

SC

Material

Base:

- Thermoplastic (1-30A models)
- Phenolic (35-60A models)

Fuse clip:

- Bimetallic copper alloy (1-30A models)
- Plated copper (35-60A models)

DIN-Rail adapters:

• DRA-1 and DRA-2



Catalog numbers:

		Terminal type				
Amps	Poles	Screw with quick-connect*	Pressure plate with quick-connect*	Box lug	Box lug with retaining clip	Fig. No.
1 to 15	1	BG3011SQ	BG3011PQ	BG3011B	_	1
	2	BG3012SQ	BG3012PQ	BG3012B	_	2
	3	BG3013SQ	BG3013PQ	BG3013B	_	3
20	1	BG3021SQ	BG3021PQ	BG3021B	_	1
	2	BG3022SQ	BG3022PQ	BG3022B	_	2
	3	BG3023SQ	BG3023PQ	BG3023B	_	3
25 to 30	1	BG3031S	BG3031P	BG3031B	_	1
	2	BG3032S	BG3032P	BG3032B	_	2
	3	BG3033S	BG3033P	BG3033B	_	3
35 to 60	1	_	_	_	G30060-1CR+	4
	2	_	_	_	G30060-2CR+	5
	3	_	_	G30060-3C**+	G30060-3CR+	6
Wire range		#10 - #14Cu	#10 - #18Cu	#6 - #14Cu (1-30A) #2 - #14Cu, #2 - #8Al (35-60A)	#2 - #14Cu, #2 - #8Al	

^{*} Quick connect rated for 20A maximum.

Dimensions - in (±0.015):




Figure 1. Figure 2. Figure 3.




Figure 4.

Figure 5.

Figure 6.

^{**} Not RoHS compliant.

⁺ Rated for #8 class H wire; 40 In.-Lbs

The only controlled copy of this data sheet is the electronic read-only version located on the Eaton network drive. All other copies of this document are by definition uncontrolled. This bulletin is intended to clearly present comprehensive product data and provide technical information that will help the end user with design applications. Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.

> 1000 Eaton Boulevard Cleveland, OH 44122 United States Eaton.com

Bussmann Division 114 Old State Road Ellisville, MO 63021 United States Eaton.com/bussmannseries

© 2023 Eaton All Rights Reserved Publication No. 1106 - BU-SB13774 January 2023

Eaton and Bussmann are valuable trademarks of Eaton in the US and other countries. You are not permitted to use the Eaton trademarks without prior written consent of Eaton.

UL is a registered trademark of the Underwriters Laboratories, Inc.

For Eaton's Bussmann series product information, call **1-855-287-7626** or visit: Eaton.com/bussmannseries

Follow us on social media to get the latest product and support information.











