Type BLC-16 Fuse Block

For 1/4" x 11/4" (6.3 x 32mm) Fuses



www.optifuse.com

(619)-593-5050

Fuse Style: 1/4" x 11/4" (6.3 x 32mm) Fuses

Material:

Body: Thermostate (UL Flame: 94V-0) **Fuse Clips:** Copper Alloy Tinned T:0.5mm **Terminal:** Copper Alloy Tinned T:0.8mm

Specifications:

Dielectric Strength for 60 seconds: 1200VAC Min

Suitable Rated Current: 25A 250V

Insulation resistance at 500V DC: 500M Min.

Temperature Rise: 30 with dummy fuse, 85 with time-delay fuse


Voltage Drop: 15mV Max.

Agency Standards and Listings:

c **FL** us

Product Dimensions: Inches [mm]

Part #	# of Pins/Legs	Terminals
BLC-16-B	no	Bent
BLC-16-B1	1	Bent
BLC-16-B2	2	Bent
BLC-16-S	no	Straight
BLC-16-S1	1	Straight
BLC-16-S2	2	Straight



Note: All specifications subject to change without notice.

Rev A 06/2007 - Page: 1/2


Code: C01-02D

Type BLC-16 Fuse Block For 1/4" x 11/4" (6.3 x 32mm) Fuses



www.optifuse.com

(619)-593-5050



Warning:

-Operation beyond the specified maximum ratings or improper use may result in damage and possible electrical arcing and/or flame.



-Avoid contact of Fuse Block with chemical solvent. Prolonged contact will damage the device performance.

Note: All specifications subject to change without notice.

Rev A 06/2007 - Page: 2/2

Code: C01-02D