



Radiall 狐

N ATTENUATOR 6 DB 6 GHZ 150W

PAGE 1/2 ISSUE 05-03-19A SERIES PART NUMBER R422006040





All dimensions are in mm. Tolerances according ISO 2768 m-H



COMPONENTS	MATERIALS	PLATING (μm)	
Body Male center contact Female center contact	BRASS BERYLLIUM COPPER BERYLLIUM COPPER	BBR 3 GOLD 0.5 OVER NICKEL PHOSPHORUS 2 GOLD 0.5 OVER NICKEL PHOSPHORUS 2	
Outer contact Insulator	PTFE	GOLD 0.3 OVER NICKEL PHOSPHORUS 2	
Gasket	SILICONE RUBBER		
Substrate Resistor Others parts	ALUMINIUM NITRIDE THICK FILM ALUMINIUM	BLACK ANODIZATION	



Technical Data Sheet N ATTENUATOR 6 DB 6 GHZ 150W

PAGE 2/2 ISSUE 05-03-19A SERIES PART NUMBER R422006040

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 2.5	2.5 - 6
V.S.W.R (≤)	1.25	1.25
Deviation(±dB)	0.75	1

Operating Frequency Range	DC - 6	GHz
Impedance	50	Ω
Nominal Attenuation	6	dB
Peak power at 25°C (1µs, 1‰)	2000	W
Average power at 25°C	150	W (Free Air Cooled)
		W (Conduction Cooled)


MECHANICAL CHARACTERISTICS

Connectors	N	Male Female	MIL C39012
Weight	1 855,2100	g	

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55/+125	°C
Storage temperature range	-55/+125	°C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS