





TNC ATTENUATOR 30 DB 6 GHZ 150W

PAGE 1/2 ISSUE 03-02-21A SERIES PART NUMBER R422130040





All dimensions are in mm. Tolerances according ISO 2768 m-H



COMPONENTS	MATERIALS	PLATING (μm)
Body Male center contact	STAINLESS STEEL BERYLLIUM COPPER	PASSIVATED. GOLD 0.5 OVER NICKEL PHOSPHORUS 2
Female center contact	BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL PHOSPHORUS 2
Outer contact		
Insulator	PTFE	
Gasket	SILICONE RUBBER	
Substrate	ALUMINIUM NITRIDE	
Resistor	THICK FILM	
Others parts	ALUMINIUM	BLACK ANODIZATION





TNC ATTENUATOR 30 DB 6 GHZ 150W

PAGE 2/2	ISSUE 03-02-21A	SERIES ATTENUATOR	PART NUMBER R422130040
-----------------	------------------------	----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 2.5	2.5 - 6
V.S.W.R (≤)	1.25	1.25
Deviation(±dB)	1.5	2.5

Operating Frequency Range	DC - 6	GHz
Impedance	50	Ω
Nominal Attenuation	30	dB
Peak power at 25°C (1µs, 1%)	2000	W
Average power at 25°C	150	W (Free Air Cooled)
		W (Conduction Cooled)


MECHANICAL CHARACTERISTICS

Connectors	TNC	Male Female	MIL C39012
Weight	1845,46	g	

ENVIRONMENTAL CHARACTERISTICS

Operating temp	erature range	-55/+125	°C	
Storage temper	ature range	-55/+125	°C	

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS