## Type: PFC2225B

#### Product Description


- · 25.0×20.0mm Max.(L×W), 27.0mm Max. Height .
- Inductance range: 0.8mH~7mH
- Rated current range:3.0A~8.0A
- · In addition to the standard versions of parameters shown here, custom designs are available to meet your exact requirements.



#### Feature


- Safety standard conformance such as UL.
- · Ideally used in TV, VCRs, OA devices.
- RoHS Compliance

#### **Dimensions (mm)**



- \* Wiring-channel position for terminals of part name 801,152 and dimension A1,B1
- \* Wiring-channel position for terminals of part name 402,502,702,502B,702B and dimension A2,B2
- Dimension does not include solder used on coil. \*

### Schematics (Bottom)



Winding start is #1,#4 or #2,#3.
#1&#4, #2&#3 : should have same polarity.

# Type: PFC2225B

### Specification

Part Name	Stamp	Inductance [MIN.](mH) (1-2) or ( 4-3) 1kHz/0.1V	Inductance Balance [MAX.] ( µ H)	D.C.R. (m Ω) [MAX.] (1-2) or (4-3) (at 20°C)	(50/60HZ) (Arms)(1-4)
PFC2225BNP-8Ø1	801	0.8	50	12.5	8.0
PFC2225BNP-152	152	1.5	80	26.0	5.0
PFC2225BNP-4Ø2	402	4.0	100	54.0	4.0
PFC2225BNP-5Ø2	502	5.0	150	81.0	3.0
PFC2225BNP-7Ø2	702	7.0	200	135.0	2.5
PFC2225BNP-5Ø2B	502B	5.0	150	61.0	3.5
PFC2225BNP-7Ø2B	702B	7.0	200	70.0	3.0

 $\therefore$ 1. Rated current: The AC current at which the temperature rise is  $\triangle t=60^{\circ}$ C.(Ta=20°C).