






STRAIGHT SCREW PLUG SOLDER TYPE CABLE .141

PAGE 1/3 ISSUE 30-01-18B SERIES NEX10 PART NUMBER R180052007







All dimensions are in mm. Tolerances according ISO 2768 m-H



COMPONENTS	MATERIALS	PLATING (μm)	
Body	BRASS.	BBR	
Center contact	BRASS.	SILVER	
Outer contact	BERYLLIUM COPPER	SILVER	
Insulator	PTFE		
Gasket	SILICONE RUBBER		
Others parts	BRASS,BRONZE	BBR	
-	-	-	
-	-	-	



Technical Data Sheet

STRAIGHT SCREW PLUG SOLDER TYPE CABLE .141

PAGE **2/3** ISSUE 30-01-18B SERIES NEX10 PART NUMBER R180052007

PACKAGING

Standard Unit Other

ELECTRICAL CHARACTERISTICS

Impedance 50 Frequency 0-20 GHz **VSWR** 1.02* 0.0150 x F(GHz) Maxi Insertion loss 0.05 √F(GHz) dB Maxi RF leakage - F(GHz)) dB Maxi - (500 Voltage rating Veff Maxi Dielectric withstanding voltage 1500 Veff mini Insulation resistance 5000 $M\Omega$ mini

MECHANICAL CHARACTERISTICS

Center contact retention

Axial force - Mating End NA N mini Axial force - Opposite end NA N mini N.cm mini NA Torque

Recommended torque

150 Mating N.cm Panel nut NA N.cm Clamp nut NA N.cm A/F clamp nut 0.0000 mm

Mating life 100 Cycles mini 9.1900 g

Weight

ENVIRONMENTAL

Operating temperature -55~+125 $^{\circ}C$ Hermetic seal NA Atm.cm3/s Panel leakage NA

SPECIFICATION

CABLE ASSEMBLY

Stripping	а	b	С	d	е	f
mm	3	0	0	0	0.85	0

Assembly instruction: NA

Recommended cable(s)

RG 402

Characteristics indicated on this data sheet are those that can be achieved with the highest performance cable. Intrinsic limitations of the cable may diminish the performance of the

Cable retention

200 - pull off N mini NA - torque N.cm

TOOLING

Part Number	Description	Hexagon

OTHER CHARACTERISTICS

IP68(1m,24h) mated condition **-110dB typical, DC to 6GHz PIM3<=-123 dBm, 2 carriers of +43dBm *Return loss and VSWR for interface:


Frequency	Return Loss	VSWR(Maxi)
0.01 GHz – 4.00 GHz	< -36 dB	1.03
4.01 GHz – 6.00 GHz	< -34 dB	1.04
6.01 – 12.00 GHz	< -30 dB	1.07
12.01 – 20.00 GHz	< -20 dB	1.22



Technical Data Sheet

STRAIGHT SCREW PLUG SOLDER TYPE CABLE .141

PAGE 3/3 ISSUE 30-01-18B SERIES NEX10 PART NUMBER R180052007



- 1
 - -Strip the cable with the cable stripping tool.
 - -Clean the cable



- 2
 - -Insert center contact until the cable
 - -Solder center contact

- 3
 - -Introduce the cable into the body until center contact contact with the insulator.
 - -Place the sub-assembly on assembly jig
 - -Solder body on the cable.
 - -Let assembly cool down before removing it from the jig.

