


# SERIES 2980

MIL-STD-883 COMPLIANT

## HIGH-VOLTAGE, HIGH-CURRENT SOURCE DRIVERS



Dwg. No. A-10.243

### ABSOLUTE MAXIMUM RATINGS at +25°C Free-Air Temperature

Output Voltage Range, V <sub>CE</sub>	
(UDS2981 and UDS2982H/R) . . . . .	5 V to 50 V
(UDS2983 and UDS2984H/R) . . . . .	35 V to 80 V
Input Voltage, V <sub>IN</sub>	
(UDS2981 and UDS2983H/R) . . . . .	15 V
(UDS2982 and UDS2984H/R) . . . . .	30 V
Output Current, I <sub>OUT</sub>	-500 mA
Ground Terminal Current, I <sub>GND</sub>	3.0 A
Power Dissipation, P <sub>D</sub>	
(any one driver) . . . . .	1.1 W
(total package) . . . . .	See Graph
Operating Temperature Range, T <sub>A</sub>	-55°C to +125°C
Storage Temperature Range, T <sub>S</sub>	-65°C to +150°C

Series UDS2980H and UDS2980R hermetically sealed source drivers link standard low-power digital logic and relays, solenoids, magnetic print hammers, stepping motors, LEDs, and lamps in applications requiring separate logic and load grounds, load supply voltages to +80 V, and load currents to 500 mA.

Types UDS2981H/R and UDS2983H/R are intended for use with 5 V logic systems (TTL, Schottky TTL, DTL and 5 V CMOS). UDS2982H/R and UDS2984H/R integrated circuits are intended for MOS interface (PMOS and CMOS) operating from supply voltages of from 6 to 16 V.

Types UDS2981H/R and UDS2982H/R will withstand an output OFF voltage of 50 V. UDS2983H/R and UDS2984H/R drivers will withstand a maximum output OFF voltage of 80 V.

Under normal operating conditions, the devices will sustain 50 mA continuously on each of the eight outputs at an ambient temperature of +85°C and with a supply voltage of 15 V. All types include input current-limiting resistors and output transient-suppression diodes. In all cases, outputs are switched ON by an active high input level.

Note that the maximum current rating may not be obtained at -55°C because of reduced beta, or at +125°C because of package power limitations.

Series UDS2980H drivers are furnished in 18-pin ceramic/metal (side-brazed) hermetic dual in-line packages. Series UDS2980R drivers are supplied in ceramic/glass (cer-DIP) hermetic packages. Both are processed to the requirements of MIL-STD-883, Class B.

The same circuits are also available in 18-pin plastic dual in-line packages (Series UDN2980A) for operation over a limited temperature range, or where higher package power dissipation is needed.

### FEATURES


- TTL, DTL, PMOS, or CMOS Compatible Inputs
- 500 mA Output Source Current Capability
- Transient-Protected Outputs
- High-Reliability Screening to MIL-STD-883, Class B
- Operating Temperature -55°C to +125°C

Always order by complete part number, e.g., **UDS2981H883**. See table on next page for differences between devices.


# SERIES 2980

## HIGH-VOLTAGE, HIGH-CURRENT SOURCE DRIVERS

### ONE OF EIGHT DRIVERS



Dwg. No. A-10,242B



Dwg. GM-003

Device Type	$V_{CE(MAX)}$	$V_{IN(MAX)}$	Applications
UDS2981H/R	50 V	15 V	TTL, DTL, 5 V CMOS
UDS2982H/R	50 V	30 V	6-15 V CMOS/PMOS
UDS2983H/R	80 V	15 V	TTL, DTL, 5 V CMOS
UDS2984H/R	80 V	30 V	6-15 V CMOS/PMOS

# SERIES 2980

## HIGH-VOLTAGE, HIGH-CURRENT SOURCE DRIVERS

ELECTRICAL CHARACTERISTICS from -55°C to +125°C (unless otherwise specified).

Characteristic	Symbol	Applicable Devices <sup>†</sup>	Temp.	Test Conditions	Fig.	Limit
Maximum Output Leakage Current	$I_{CEX}$	UDS2981/82		$V_{IN} = 0.25 \text{ V}^*, V_S = 50 \text{ V}$	1	200 $\mu\text{A}$
		UDS2983/84		$V_{IN} = 0.25 \text{ V}^*, V_S = 80 \text{ V}$	1	200 $\mu\text{A}$
Maximum Collector-Emitter Saturation Voltage	$V_{CE(SAT)}$	UDS2981/83	-55°C	$V_{IN} = 2.4 \text{ V}, I_{OUT} = -100 \text{ mA}$	2	2.0 V
				$V_{IN} = 2.4 \text{ V}, I_{OUT} = -200 \text{ mA}$	2	2.1 V
			+25°C	$V_{IN} = 2.4 \text{ V}, I_{OUT} = -350 \text{ mA}$	2	2.0 V
			+125°C	$V_{IN} = 2.4 \text{ V}, I_{OUT} = -100 \text{ mA}$	2	1.8 V
				$V_{IN} = 2.4 \text{ V}, I_{OUT} = -200 \text{ mA}^{**}$	2	1.9 V
		UDS2982/84	-55°C	$V_{IN} = 5.0 \text{ V}, I_{OUT} = -100 \text{ mA}$	2	2.0 V
				$V_{IN} = 5.0 \text{ V}, I_{OUT} = -200 \text{ mA}$	2	2.1 V
			+25°C	$V_{IN} = 5.0 \text{ V}, I_{OUT} = -350 \text{ mA}$	2	2.0 V
			+125°C	$V_{IN} = 5.0 \text{ V}, I_{OUT} = -100 \text{ mA}$	2	1.8 V
				$V_{IN} = 5.0 \text{ V}, I_{OUT} = -200 \text{ mA}^{**}$	2	1.9 V
Maximum Input Current	$I_{IN(ON)}$	All		$V_{IN} = 2.4 \text{ V}$	3	295 $\mu\text{A}$
				$V_{IN} = 3.85 \text{ V}$	3	600 $\mu\text{A}$
				$V_{IN} = 12 \text{ V}$	3	2.3 mA
	$I_{IN(OFF)}$	UDS2981/82		$V_{IN} = 0 \text{ V}, V_S = 50 \text{ V}$	3	10 $\mu\text{A}$
		UDS2983/84		$V_{IN} = 0 \text{ V}, V_S = 80 \text{ V}$	3	10 $\mu\text{A}$
Minimum Output Source Current	$I_{OUT}$	UDS2981/83		$V_{IN} = 2.4 \text{ V}, V_{CE} = 2.2 \text{ V}$	2	-200 mA
		UDS2982/84		$V_{IN} = 5.0 \text{ V}, V_{CE} = 2.2 \text{ V}$	2	-200 mA
Maximum Supply Current (Outputs Open)	$I_S$	UDS2981	+25°C	$V_{IN} = 2.4 \text{ V}^*, V_S = 50 \text{ V}$	4	10 mA
		UDS2982		$V_{IN} = 5.0 \text{ V}^*, V_S = 50 \text{ V}$	4	10 mA
		UDS2983		$V_{IN} = 2.4 \text{ V}^*, V_S = 80 \text{ V}$	4	10 mA
		UDS2984		$V_{IN} = 5.0 \text{ V}^*, V_S = 80 \text{ V}$	4	10 mA
Maximum Turn-ON Delay Time	$t_{pHL}$	UDS2981/82	+25°C	$V_S = 35 \text{ V}, R_L = 175 \Omega$	7	2.0 $\mu\text{s}$
		UDS2983/84		$V_S = 50 \text{ V}, R_L = 250 \Omega$	7	2.0 $\mu\text{s}$
Maximum Turn-OFF Delay Time	$t_{pLH}$	UDS2981/82	+25°C	$V_S = 35 \text{ V}, R_L = 175 \Omega$	7	10 $\mu\text{s}$
		UDS2983/84		$V_S = 50 \text{ V}, R_L = 250 \Omega$	7	10 $\mu\text{s}$
Maximum Clamp Diode Leakage Current	$I_R$	UDS2981/82		$V_{IN} = 0.25 \text{ V}^*, V_S = 50 \text{ V}$	5	50 $\mu\text{A}$
		UDS2983/84		$V_{IN} = 0.25 \text{ V}^*, V_S = 80 \text{ V}$	5	50 $\mu\text{A}$
Maximum Clamp Diode Forward Voltage	$V_F$	ALL		$I_F = 200 \text{ mA}$	6	1.75 V

\*All inputs simultaneously.


\*\*Pulsed test.

†Complete part number includes a terminal letter that indicates package (H = ceramic/metal side-brazed, R = ceramic/glass cer-DIP).

# SERIES 2980 HIGH-VOLTAGE, HIGH-CURRENT SOURCE DRIVERS


## TEST FIGURES

**Figure 1**




Dwg. No. A-11.083

**Figure 2**




Dwg. No. A-11.084

**Figure 3**




Dwg. No. A-11.085

**Figure 4**




Dwg. No. A-11.086

**Figure 5**




Dwg. No. A-11.087

**Figure 6**




Dwg. No. A-11.088

**Figure 7**



Dwg. No. A-13.26A

**INPUT CURRENT  
AS A FUNCTION OF INPUT VOLTAGE**




Dwg. No. A-11.11!

# SERIES 2980

## HIGH-VOLTAGE, HIGH-CURRENT SOURCE DRIVERS


### RECOMMENDED PEAK COLLECTOR CURRENT AS A FUNCTION OF DUTY CYCLE SERIES UDS2980H

**UDS2981/82H**




Dwg. No. A-11.078B

**UDS2981/82H**




Dwg. No. A-11.076B

**ALL DEVICES**




Dwg. No. A-11.079B

**ALL DEVICES**




Dwg. No. A-11.080B

**UDS2983/84H**



Dwg. No. A-11.077A

**UDS2983/84H**




Dwg. No. A-11.081A


**SERIES 2980**  
**HIGH-VOLTAGE, HIGH-CURRENT SOURCE DRIVERS**  
**MIL-STD-883 COMPLIANT**

**RECOMMENDED PEAK COLLECTOR CURRENT  
 AS A FUNCTION OF DUTY CYCLE**  
**SERIES UDS2980R**


**UDS2981/82R**




**UDS2981/82R**




**ALL DEVICES**




**ALL DEVICES**



**UDS2983/84R**



**UDS2983/84R**



Dwg. No. A-12.403

Dwg. No. A-12.404