



All dimensions are in mm; tolerances according to ISO 2768 m-H

Interface

According to IEC 61169-4, EN 122190, DIN 47223

Documents

Application note AN001 "Calibration Services"

Material and plating

Connector parts

- Center conductor plug side
- Center conductor plug side
- Outer conductor
- Coupling nut
- Gasket

Material

- Brass
- CuBe
- Brass
- Stainless steel
- NBR

Plating

- Gold, min. 1.27 µm, over nickel
- Gold, min. 1.27 µm, over nickel
- Gold, min. 1.27 µm, over nickel
- Passivated

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG

RF_35/09.14/6.2

Electrical data

Insertion loss ≤ 0.05 dB, 0.2 GHz to 8 GHz

Mechanical data

Mating cycles ≥ 500
 Maximum torque 35 Nm
 Recommended torque 2.26 Nm
 Airline dimensions at 23 °C:
 - Diameter outer conductor 16.060 mm \pm 0.010 mm
 - Diameter inner conductor 6.975 mm \pm 0.005 mm
 - Length outer conductor 50.00 mm + 0.02 mm
 - Length inner conductor 49.98 mm - 0.02 mm
 - Length difference ≤ 0.06 mm
 (outer conductor – inner conductor)

Calculated data (non warranted)

Lossless characteristic impedance¹ 50 Ω \pm 0.10 Ω
 Return loss² ≥ 45 dB, 0.2 GHz to 4 GHz
 ≥ 40 dB, 4 GHz to 8 GHz

1. The lossless characteristic impedance is calculated from the specified diameters of the inner and outer conductor.
2. The return loss is calculated from the characteristic impedance, the skin depth and the connector interface.

General standard definitions

For proper work the vector network analyzer (VNA) used needs a model describing the electrical behaviour of this calibration standard. Depending on the VNA type different models, units and terms are used and have to be entered into the VNA. All values are based on typical geometry and plating.

- Offset Z_o / Impedance / Z_o 50 Ω
 - Offset Delay 166.870 ps
 - Length (electrical) / Offset Length 50.026 mm
 - Offset Loss 0.80 G Ω /s
 - Loss 0.0116 dB/ $\sqrt{\text{GHz}}$

Environmental data

Operating temperature range³ +20 °C to +26 °C
 Storage temperature range 0 °C to +50 °C
 RoHS compliant

3. This range is a recommendation. However, the airline can be used in a wider range. Any temperature change from 23 °C results in dimensional changes.

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG

RF_35/09.14/6.2

7-16

Airline Plug / Jack

60S101-K050

Declaration of calibration options

Factory Calibration

Standard delivery for this calibration standard includes a Factory Calibration. The Calibration Certificate issued reports individual mechanical calibration results, traceable to national / international standards. Model based standard definitions are reported in an Agilent/Keysight, Rohde & Schwarz and Anritsu compatible VNA format.

Accredited Calibration

Not available.

For further, more detailed information see application note AN001 on the Rosenberger homepage.

Calibration interval

Recommendation 12 months

Packing

Standard 1 pce in box
 Weight 142.8 g/pce
 Center conductor loose in an acrylic glass tube

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Herbert Babinger	14.03.05	Martin Moder	11.10.23	g00	23-1603	Matthias Gehl	11.10.23
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de						Tel. : +49 8684 18-0 Email : info@rosenberger.de	
							Page 3 / 3