# AMDLA3020S MOLDED INDUCTOR

Request Samples 🕥

#### **FEATURES**

- Shielded construction
- Soft saturation
- Low DCR per cubic mm
- Designed for switching frequencies between 100KHz-5MHz
- Automotive option available upon request

### **ELECTRICAL SPECIFICATIONS @ 25°C**

PART NUMBER*	INDUCTANCE (uH)	TOLERANCE (%)	IRMS (A)	ISAT (A)	DC RESISTANCE (mΩ)		ТҮРЕ
					TYP	MAX	
AMDLA3020S-R22MT	0.22	20	10.0	16	8	10	Lead Frame
AMDLA3020S-R33MT	0.33	20	9.0	14	12	15	Lead Frame
AMDLA3020S-R47MT	0.47	20	8.0	12	15	18	Lead Frame
AMDLA3020S-R68MT	0.68	20	7.0	10	22	26	Lead Frame
AMDLA3020S-1R0MT	1.0	20	5.0	8.0	25	30	Lead Frame
AMDLA3020S-1R5MT	1.5	20	4.2	6.0	34	39	Lead Frame
AMDLA3020S-2R2MT	2.2	20	3.3	4.8	60	69	Lead Frame
AMDLA3020S-3R3MT	3.3	20	2.8	4.0	70	83	Lead Frame
AMDLA3020S-4R7MT	4.7	20	2.4	3.5	120	144	Lead Frame
AMDLA3020S-6R8MT	6.8	20	1.6	3.0	153	184	Lead Frame
AMDLA3020S-100MT	10.0	20	1.3	1.8	224	260	Lead Frame

\* Please refer to Part Identification section

#### **Test Conditions**

Inductance: 1 MHz, 1 V, 0 Adc Humidity Range: 65% RH Temperature Rise Current: Current measured at  $\Delta$  T of 40°C Saturation Current: Current measured at  $\Delta$  L of 30%

#### PART BUILDER



Series

**1. Tolerance:** M = 20%

Inductance\* Tol. <sup>1</sup>

2. Packaging: B = Bulk

T = Tape and Reel (3,000pcs/reel)

Packaging<sup>2</sup>

\*Refer to Electrical Specification table

## GENERAL SPECIFICATIONS

**Operating Temperature:** -55°C to +125°C with (40°C rise) Irms current.


Maximum Part Temperature: +125°C Components Storage Temperature: -55°C to +125°C

Tape and Reel Packaging Temperature: -20°C to +65°C MSL: Level 1

### MATERIALS

Core:Metal AlloyWire:CopperTerminal:Tin PlatingInk:Black


### **PRODUCT DIMENSIONS**





Revised 09/16/19


oy ng







#### **RECOMMENDED REFLOW PROFILE**



ZONE	DESCRIPTION	TEMPERATURE	TIMES
1	Preheat	T <sub>smin</sub> <sup>∼</sup> T <sub>smax</sub> 150°C <sup>∼</sup> 180°C	60 ~ 120 sec.
2	Reflow	Τ <sub>∟</sub> 230℃	30 ~ 40 sec.
3	Peak Heat	Т <sub>Р</sub> 250°С+0/-5°С	10 sec. MAX




# AMDLA3020S MOLDED INDUCTOR




#### PACKAGING

Tape and Reel:	3,000
Units per Carton:	24,000
T&R per Carton:	8
Weight per Carton:	13.5 kg
Weight per Unit:	0.45 g
Carton Dimensions:	360 x 360 x 400 mm



ТҮРЕ	А	В	С	D
13" x 12 mm	12.4 +2/-0	$100.0 \pm 0.5$	13.0 +0.5/-0.2	330.0



1.5

This product is commercial off-the-shelf (COTS) and not specifically designed for automotive, military, aviation, aerospace, implantable, life-dependent medical or safety applications. This product is not recommended for use in any application requiring high reliability in which component failure could result in loss of life and/or property damage without prior written approval from Abracon. Specifications are subject to change without notice. Contact Abracon for more information.

3.8 ± 0.1 3.4 ± 0.1 2.3 ± 0.1 8.0 ± 0.1 12.0 ± 0.3 5.5 ± 0.1 0.3 ± 0.05



Headquarters: 5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858