]								RE	VIS	10	NS								
							TR	Г			DE	sc	RIP						D	ATE	T	AP	PR	OVE	
						ŀ	Α	Cor Add	nver 1 ve	t to	Mi	lit	ary	Dra		g fo	orma	ıt.	20	DEC 86	1	M	24,	K.	<i>\</i>
																					i		_		
nev 1				·-	1			1	1						1		1	.							1
		<u></u>									_						I							—	
PAGE REV STAT		REV	A	A	A	A	A	A	A	A	A	A	A												
PAGE REV STAT		REV	_	2	3	4	5	6	A 7	_	A 9	A 10													
PAGE REV STAT OF PAGES Defense Eli Supply Cen	ectroni	PAG		P P I	3 EPA	4 REI	5 B	6 2/1	7	_	9	10	11 Th all De	is d De epar	draw part tmer	ing men nt of	is a ts a f Def	vaila nd <i>A</i> ense	ible Agen	R	use of	the			
PAGE REV STAT OF PAGES Defense Ele Supply Cen Dayton, Oh Original dat of drawing:	ectroni iter io	PAG cs			EPA ECK Q	A REIL	B'	6 */2 YO	7 un	8 ste	9	10 C	TI	is of De	parti tmer CI M	ing men it of ICRO MOS ONOL	is a ts a f Det OCIR DAT ITH	vaila nd A ense CUIT A SE IC S	Agen S, ELEC	for cies DIGI TOR/ CON	of TAI	the	ł I Gł	H-SF	EE
REV PAGE REV STAT OF PAGES Defense Eli Supply Cen Dayton, Oh Original dat of drawing: 27 Januar	ectroni iter io	PAG cs		P P I	EPA ECK Q	A REIL	B B B ODE	6 Y 12 Y 60 Y 10 Y 10 Y 10 Y 10 Y 10 Y 10 Y 10 Y 1	7 un	8 ste	9	10 C	TI	is d De epar	parti tmer CI M	ing men it of ICRO MOS ONOL	is a ts a f Det OCIR DAT ITH	vaila nd A ense CUIT A SE	Agen S, ELEC	for cies DIGI TOR/ CON	of TAI	the	ł I Gł	H-SF	EE

1. SCOPE	
1.1 Scope. This drawing describes device r 1.2.1 of MIL-STD-883, "Provisions for the use devices".	requirements for class B microcircuits in accordance with of MIL-STD-883 in conjunction with compliant non-JAN
1.2 Part number. The complete part number	shall be as shown in the following example:
Drawing number Device type (1.2.1)	E X T T
1.2.1 <u>Device type</u> . The device type shall i	dentify the circuit function as follows:
Device type Generic number	Circuit function
01 54HC151	Eight-input data selector/ multiplexer, with enable
1.2.2 <u>Case outlines</u> . The case outlines sha follows:	ll be as designated in appendix C of MIL-M-38510, and as
Outline letter	Case outline
E 2	D-2 (16-lead, 1/4" x 7/8"), dual-in-line package C-2 (20-terminal, .350" x .350"), square chip carrier package
1.3 Absolute maximum ratings. $1/$	
Supply voltage range	
Junction temperature (T_{J})	+175°C
1.4 Recommended operating conditions.	
Supply voltage Case operating temperature range (T_C) Input rise or fall time: $V_{CC} = 2.0 \ V_{CC} = 4.5 \ V_{CC} = 4.5 \ V_{CC} = 6.0 \ V_{CC} = 0.0 $	
$\frac{1}{2}$ Unless otherwise specified, all voltages $\frac{2}{7}$ For $T_C = +100^{\circ}C$ to $+125^{\circ}C$, derate linear	are referenced to ground. ly at 12 mW/°C.

3/ When a thermal resistance value is included in MIL-M-38510, appendix C, it shall supersede the value indicated herein.

8411	ITADV		14/1	NO
IVIIL	.ITARY	UKA	WI	NG

DEFENSE ELECTRONICS SUPPLY CENTER DAYTON, OHIO

SIZE		IDENT. NO.	DWG NO).		
A	1	4933		84128		
		REV A		PAGE	2	_

2. APPLICABLE DOCUMENTS

2.1 Government specification and standard. Unless otherwise specified, the following specification and standard, of the issue listed in that issue of the Department of Defense Index of Specifications and Standards specified in the solicitation, form a part of this drawing to the extent specified herein.

SPECIFICATION

MILITARY

MIL-M-38510

- Microcircuits, General Specification for.

STANDARD

MILITARY

MIL-STD-883

Test Methods and Procedures for Microelectronics.

(Copies of the specification and standard required by manufacturers in connection with specific acquisition functions should be obtained from the contracting activity or as directed by the contracting activity.)

2.2 Order of precedence. In the event of a conflict between the text of this drawing and the references cited herein, the text of this drawing shall take precedence.

3. REQUIREMENTS

- 3.1 Item requirements. The individual item requirements shall be in accordance with 1.2.1 of MIL-STD-883, "Provisions for the use of MIL-STD-883 in conjunction with compliant non-JAN devices" and as specified herein.
- 3.2 Design, construction, and physical dimensions. The design, construction, and physical dimensions shall be as specified in MIL-M-38510 and herein.
 - 3.2.1 Terminal connections. The terminal connections shall be as specified on figure 1.
- 3.2.2 <u>Truth table and logic diagram</u>. The truth table and logic diagram shall be as specified on figure 2.
 - 3.2.3 Case outlines. The case outlines shall be in accordance with 1.2.2 herein.
- 3.3 Electrical performance characteristics. Unless otherwise specified, the electrical performance characteristics are as specified in table I and apply over the full recommended case operating temperature range.
- 3.4 Marking. Marking shall be in accordance with MIL-STD-883 (see 3.1 herein). The part shall be marked with the part number listed in 1.2 herein. In addition, the manufacturer's part number may also be marked as listed in 6.4 herein.
- 3.5 Certificate of compliance. A certificate of compliance shall be required from a manufacturer in order to be listed as an approved source of supply in 6.4. The certificate of compliance submitted to DESC-ECS prior to listing as an approved source of supply shall state that the manufacturer's product meets the requirements of MIL-STD-883 (see 3.1 herein) and the requirements herein.
- 3.6 Certificate of conformance. A certificate of conformance as required in MIL-STD-883 (see 3.1 herein) shall be provided with each lot of microcircuits delivered to this drawing.

MILITARY DRAWING	SIZE A	CODE IDENT. NO. 14933	DWG NO. 84128
DEFENSE ELECTRONICS SUPPLY CENTER DAYTON, OHIO		REV A	PAGE 3

Test					Li	nits	Unit
		Conditi -55°C < T _C < unless otherwi	subgroups	Min	Max		
High-level output voltage	V _{ОН}	V _{IN} = V _{IH} or V _{IL} I ₀ < 20 μA	V _{CC} = 2.0 V	1, 2, 3	1.9	 	٧
	 		V _{CC} = 4.5 V		4.4		
	 		V _{CC} = 6.0 V	 	5.9		
		$ V_{IN} = V_{IH} \text{ or } V_{IL}$ $ I_0 \leq 4.0 \text{ mA}$	V _{CC} = 4.5 V		3.7		
		$V_{IN} = V_{IH} \text{ or } V_{IL}$ $ I_0 \leq 5.2 \text{ mA}$	Y _{CC} = 6.0 V		5.2		
Low-level output voltage	V _{OL}	$ V_{IN} = V_{IH} \text{ or } V_{IL}$ $ I_0 < 20 \mu A$	V _{CC} = 2.0 V	1, 2, 3		0.1	٧
	 	1	V _{CC} = 4.5 V			0.1	
	 		V _{CC} = 6.0 V	 		0.1	
		V _{IN} = V _{IH} or V _{IL} I ₀ < 4.0 mA	V _{CC} = 4.5 V			0.4	
			V _{CC} = 6.0 V			0.4	

See footnotes at end of table.

MILITARY DRAWING DEFENSE ELECTRONICS SUPPLY CENTER DAYTON, OHIO	SIZE	14933	DWG NO. 84128	
		REV A	PAGE	4

V_{CC} = 2.0 V

V_{CC} = 4.5 V

 $V_{CC} = 6.0 \text{ V}$

V_{CC} = 2.0 V

| V_{CC} = 4.5 V

 $V_{CC} = 6.0 \text{ V}$

1, 2, 3 | 1.5 |

1, 2, 3

3.15

4.2

0.3 j

0.9

1.2

٧

٧

High-level input voltage

Low-level input voltage

AIH

VIL

		Y	<u></u>				
	TABLE I.	Electrical performance	characteristics -	Continued.			
	Ţ		1/		Limit	s	
Test	Symbol 	Condition -55°C < TC <	ns <u>+</u> / +125°C	Group A subgroups	Min M	ax	Unit
	<u> </u>	unless otherwis	e specified				<u> </u>
Input capacitance	CIN	VIN = 0 V T _C = +25°	C	4	1	0	pF
Quiescent current	Icc	V _{CC} = 6.0 V _{IN} = V	CC or GND	1, 2, 3	116	0	μ А
Input leakage current	IIN	$V_{CC} = 6.0$ $V_{IN} = V_{IN}$	CC or GND	1, 2, 3	±	1	μА
Functional tests	i	See 4.3.1d		7, 8			
Propagation delay time, address	tpHL1	T _C = +25°C C ₁ = 50 pF *10%	V _{CC} = 2.0 V	9	2	50	ns
inputs to Y or W		See figure 3	V _{CC} = 4.5 V	 	1	50	
2/	İ		V _{CC} = 6.0 V			43 	
=	i ! !	 T _C = -55°C, +125°C C _L = 50 pF ±10%	V _{CC} = 2.0 V	10, 11	3	75 I	ns
	i 	 See figure 3	V _{CC} = 4.5 V	— 		75	
			V _{CC} = 6.0 V	 		64	
Propagation delay time, data inputs	tpHL2	T _C = +25°C C _I = 50 pF ±10%	V _{CC} = 2.0 V	9	2	10	ns
to Y or W	1	See figure 3	V _{CC} = 4.5 V		İ	42	
<u>2</u> /			$V_{CC} = 6.0 \text{ V}$		i i	კ6	
_		T _C = -55°C, +125°C C _L = 50 pF ±10%	V _{CC} = 2.0 V	10, 11	3	15	ns
		See figure 3	V _{CC} = 4.5 V	 		63	
	 		V _{CC} = 6.0 V			54	

See footnotes at end of table.

MILITARY DRAWING DEFENSE ELECTRONICS SUPPLY CENTER DAYTON, OHIO	SIZE	14933	DWG NO. 84128	
		REV A	PAGE	5

Test	 Symbol	Symbol Conditions $\frac{1}{2}$			Limits		Unit
	Jan Jan Jan Jan Jan Jan Jan Jan Jan Jan	Condition -55°C < T _C < unless otherwise	Group A subgroups	Min	Max		
Propagation delay time, strobe to Y	t _{PHL3}	T _C = +25°C C _L = 50 pF ±10%	V _{CC} = 2.0 V	9		155	ns
or W		See figure 3	V _{CC} = 4.5 V			 31 	! ! !
2/			V _{CC} = 6.0 V			26	
		T _C = -55°C, +125°C C _L = 50 pF ±10%	V _{CC} = 2.0 V	10, 11		235	ns
		See figure 3	V _{CC} = 4.5 V			47	
			V _{CC} = 6.0 V			40	
Transition time	t _{THL}	 T _C = +25°C C ₁ = 50 pF ±10%	V _{CC} = 2.0 V	9		75	ns
			V _{CC} = 4.5 V		1	15	-
<u>3</u> /			V _{CC} = 6.0 V			13	
_		T _C = -55°C, +125°C C _L = 50 pF *10%	V _{CC} = 2.0 V	10, 11	1	110	ns
			V _{CC} = 4.5 V			22	İ
			V _{CC} = 6.0 V	—j j	İ	19	İ

For a power supply of 5 V ±10 percent, the worst case output voltages (V_{OH} and V_{OL}) occur for HC at 4.5 V. Thus, the 4.5 V values should be used when designing with this supply. Worst case V_{IH} and V_{IL} occur at V_{CC} = 5.5 V and 4.5 V respectively. (The V_{IH} value at 5.5 V is 3.85 V.) The worst case leakage current (I_{IN} , I_{CC} and I_{OZ}) occur for CMOS at the higher voltage and so the 6.0 V values should be used. Power dissipation capacitance (C_{PD}), typically 110 pF, determines the no load dynamic power consumption, $P_D = C_{PD} V_{CC} 2^f + I_{CC} V_{CC}$, and the no load dynamic current consumption, $I_S = C_{PD} V_{CC}$ f⁺ I_{CC} .

2/ Propagation delay times at V_{CC} = 2.0 V and V_{CC} = 6.0 V shall be guaranteed, if not tested to the specified parameters.


the specified parameters.

Transition time, if not tested, shall be guaranteed to the specified limits.

MILITARY DRAWING	SIZE A	14933	DWG NO. 84128	
DEFENSE ELECTRONICS SUPPLY CENTER DAYTON, OHIO		REV A	PAGE 6	



Case E



Case 2





FIGURE 1. Terminal connections (top view).

MILITARY DRAWING DEFENSE ELECTRONICS SUPPLY CENTER DAYTON, OHIO	SIZE CODE IDENT. NO. 14933		DWG NO. 84128		
		REV A	PAGE	7	

Device type 01

	1	nputs	0u t	puts	
Select			Strobe	ı Y	W
С	В	Α	\$, 	"
Х	Х	X	Н	L	Н
L	L	L	L	DO	DO
L	L	Н	L	ΙD	D1
L	Н	L	L	D2	D2
L	Н	Н	L	D3	D3
Н	L	L	L	D4	D4
Н	L	Н	L	D5	D5
Н	Н	L	L	D6	D6
Н	Н	Н	L	D7	D7



H = High level, L = low level, X = Don't care

DO, D1 and D7 = the level of the respective D input

FIGURE 2. Truth table and logic diagram.

Device type 01




FIGURE 3. Switching waveform.

MILITARY DRAWING

DEFENSE ELECTRONICS SUPPLY CENTER DAYTON, OHIO

SIZE	E CODE IDENT. NO.		DWG NO			
А	14933		84128			
		REV	А		PAGE	8

- 3.7 Notification of change. Notification of change to DESC-ECS shall be required in accordance with MIL-STD-883 (see 3.1 herein).
- 3.8 <u>Verification and review</u>. DESC, DESC's agent, and the acquiring activity retain the option to reveiw the manufacturer's facility and applicable required documentation. Offshore documentation shall be made available onshore at the option of the reviewer.
 - 4. QUALITY ASSURANCE PROVISIONS
- 4.1 Sampling and inspection. Sampling and inspection procedures shall be in accordance with section 4 of MIL-M-38510 to the extent specified in MIL-STD-883 (see 3.1 herein).
- 4.2 <u>Screening.</u> Screening shall be in accordance with method 5004 of MIL-STD-883, and shall be conducted on all devices prior to quality conformance inspection. The following additional criteria shall apply:
 - a. Burn-in test (method 1015 of MIL-STD-883).
 - (1) Test condition A, B, C, or D using the circuit submitted with the certificate of compliance (see 3.5 herein).
 - (2) $T_A = +125^{\circ}C$, minimum.
 - b. Interim and final electrical test parameters shall be as specified in table II herein, except interim electrical parameter tests prior to burn-in are optional at the discretion of the manufacturer.
- 4.3 Quality conformance inspection. Quality conformance inspection shall be in accordance with method 5005 of MIL-STD-883 including groups A, B, C, and D inspections. The following additional criteria shall apply.
 - 4.3.1 Group A inspection.
 - a. Tests shall be as specified in table II herein.
 - b. Subgroups 5, 6, and 8 in table I, method 5005 of MIL-STD-883 shall be omitted.
 - c. Subgroup 4 ($C_{\rm IN}$ measurement) shall be measured only for the initial test and after process or design changes which may affect input capacitance.
 - d. Subgroup 7 tests sufficient to verify the truth table.
 - 4.3.2 Groups C and D inspections.
 - a. End-point electrical parameters shall be as specified in table II herein.
 - b. Steady-state life test (method 1005 of MIL-STD-883) conditions:
 - Test condition A, B, C, or D using the circuit submitted with he certificate of compliance (see 3.5 herein).
 - (2) $T_A = +125$ °C, minimum.
 - (3) Test duration: 1,000 hours, except as permitted by appendix B of MIL-M-38510 and method 1005 of MIL-STD-883.

MILITARY DRAWING DEFENSE ELECTRONICS SUPPLY CENTER DAYTON, OHIO	SIZE A	14933	DWG NO. 84128	
		REV A	PAGE 9	

TABLE II. Electrical test requirements.

MIL-STD-883 test requirements	Subgroups (per method 5005, table I)
Interim electrical parameters (method 5004) 	
Final electrical test parameters (method 5004) 	1*, 2, 9
Group A test requirements (method 5005)	1, 2, 3, 4, 7, 9, 10, 11**
Groups C and D end-point electrical parameters (method 5005)	1, 2, 3
Additional electrical subgroups for group C periodic inspections	

* PDA applies to subgroup 1.

5. PACKAGING

5.1 Packaging requirements. The requirements for packaging shall be in accordance with MIL-M-38510.

6. NOTES

- 6.1 <u>Intended use.</u> Microcircuits conforming to this drawing are intended for use when military specifications do not exist and qualified military devices that will perform the required function are not available for OEM application. When a military specification exists and the product covered by this drawing has been qualified for listing on QPL-38510, the device specified herein will be inactivated and will not be used for new design. The QPL-38510 product shall be the preferred item for all applications.
 - 6.2 Replaceability. Replaceability is determined as follows:
 - a. Microcircuits covered by this drawing will replace the same generic device covered by a contractor-prepared specification or drawing.
 - b. When a QPL source is established, the part numbered device specified in this drawing will be replaced by the microcircuit identified as part number M38510/66201B--.
- 6.3 Comments. Comments on this drawing should be directed to DESC-ECS, Dayton, Ohio 45444, or telephone 513-296-5375.

MILITARY DRAWING DEFENSE ELECTRONICS SUPPLY CENTER	SIZE	14933			
DAYTON, OHIO		REV A		PAGE	10

^{**} Subgroups 10 and 11, if not tested, shall be guaranteed to the specified limits in table I.

6.4 Approved sources of supply. Approved sources of supply are listed herein. Additional sources will be added as they become available. The vendors listed herein have agreed to this drawing and a certificate of compliance (see 3.5 herein) has been submitted to DESC-ECS.

Military drawing part number	Vendor CAGE number	Vendor similar part number 1/	Replacement military specification part number
8412801EX	27014 04713 18714	 MM54HC151J/883B 54HC151/BEAJC CD54HC151F/3A	M38510/66201BEX
84128012X	04713	 54HC151M/B2CJC 	M38510/66201B2X

Vendor CAGE number	Vendor name and address		
04713	Motorola, Inc. 7402 S. Price Road Tempe, AZ 85283		
27014	National Semiconductor 2900 Semiconductor Drive Santa Clara, CA 95051		
18714	RCA Corporation Route 202 Somerville, NJ 08876		

MILITARY DRAWING	SIZE	CODE IDENT, NO. DWG NO.	
_	A	14933	84128
DEFENSE ELECTRONICS SUPPLY CENTER DAYTON, OHIO		REV A	PAGE

11