



# Product: FSNS59BNCU-25

ProSNS RG-59 Universal BNC Coax Compression Connector

## **Product Description**

ProSNS RG59 Universal BNC compression connector, non-blind entry with split ferrule design, polymer compression sleeve for easy insertion & lowest possible tool compression force. Universal BNC connector for standard or quad-shield RG59 cable. 25 per Pack

### **Technical Specifications**

#### **Product Overview**

Suitable Applications:	CCTV, Security Cameras, Video			
Physical Characteristics (Overall)				
Packaging:	25 Pack			
Number of Pieces:	1			

#### Connectors

Materials			
Description	Material		
Nut	Nickel/Tin Plated Brass		
O-Ring	Ethylene Propylene		
Body	Nickel/Tin Plated Brass		
Contact	Gold Plated		
Electrical	Characteristics		
Impedance			
Nominal Cha	Nominal Characteristic Impedance		
75 Ohm	75 Ohm		

#### Return Loss (RL)

Frequency [MHz] ≥-32 dB up to 1 GHz typical		
Electrical Characteristics Notes:	Salt Fog: Passes 1000 hours ANSI/SCTE 143 2007, RFI Shielding: -85 dB (60% bonded foil), All Belden ProSNS connectors meet or exceed SCTE return loss standards.	

#### **Temperature Range**

Operating Temperature Range:	-40°F (-40°C) to 140°F (60°C)

## **Mechanical Characteristics**

Footprint/Type:	Coax
Connector Interface Type:	BNC
Gender:	Male - plug
Connector Series Name:	ProSNS
Color Band:	Red
Locking:	No
Tool Compatibility:	CPLCCT-SLMR or CPSNSCT-596 (compression), PSA59/6 (strip)

Termination Type:	Compression		
Cable Center Conductor Diameter Limits:	.03170339 inch		
Cable Dielectric Diameter Limits:	.144157 inch		
Cable Outer Jacket Diameter Limits:	.232273 inch		
Cable Insertion Force:	20 lbf		
Cable Retention Force:	40 lbf		
Standards			
RG Type:	59		
Applicable Environmental and Other Programs			
Environmental Space:	Indoor/Outdoor		
EU CE Mark:	Yes		
Suitability			
Suitability - Indoor:	Yes		
Suitability - Outdoor:	Yes		
Plenum/Non-Plenum			
Plenum (Y/N):	No		
Related Part Numbers			
Variants			
Item # Color UPC			
FSNS59BNCU-25 No Color 8456710	02584		
Patent:	This product has one or more applicable patents. More information on patents can be found at https://www.belden.com/patents-		
Product Notes			
Notes:	All Belden ProSNS connectors meet or exceed SCTE return loss standards.		
listory			
Update and Revision:	Revision Number: 0.132 Revision Date: 03-04-2023		

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.