

STRAIGHT ADAPTER

R191.996.130

Série : **ADAPTER**



E = Scale : 1/1



All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
BODY CENTER CONTACT OUTER CONTACT INSULATOR GASKET OTHERS PARTS	BERYLLIUM COPPER BERYLLIUM COPPER PTFE	NPGR NPGR
-	-	-

Issue: 1107 A

In the effort to improve our products, we reserve the rights to make changes judged to



STRAIGHT ADAPTER

R191.996.130

Série : **ADAPTER**

PACKAGING

Standard	Unit	Other
100	'W' option	Contact us

SPECIFICATION

ELECTRICAL CHARACTERISTICS

 $\begin{array}{ccc} \text{Impedance} & & \textbf{50} \;\; \Omega \\ \text{Frequency} & & \textbf{0-6} \;\; \text{GHz} \end{array}$

VSWR 1.25* + 0,0000 x F(GHz) Maxi

Insertion loss RF leakage 0.15* $\sqrt{F(GHz)}$ dB Maxi - (NA - F(GHz)) dB Maxi

Voltage rating 335 Veff Maxi Dielectric withstanding voltage Insulation resistance 500 Veff mini 500 M Ω mini

ENVIRONMENTAL

Operating -55/+125 ° C Hermetic seal NA Atm.cm3/s

Panel leakage NA

MECHANICAL CHARACTERISTICS

Center contact retention

Axial force – Mating end 7 N mini Axial force – Opposite end 7 N mini Torque NA N.cm mini

Recommended torque

Mating **0** N.cm

SMP-MAX 0 N.cm SMP-COM 0 N.cm

Panel nut NA N.cm

Mating life 100 Cycles mini

Weight **0,2860** g

OTHER CHARACTERISTICS

*VSWR:up to 3GHz; 3-6GHz,1.35 max

*Coaxial Transmission Line Only

*Slide type receptacle+Bullet+Snap type receptacle

Typical VSWR(Board to Board connection):

0-3GHz, 1.2max

Power handling (typical): >120W@3GHz at 25°C

Radial working angle: 3°min Axial working range: 2mm

Issue: 1107 A

In the effort to improve our products, we reserve the rights to make changes judged to be necessary.




STRAIGHT ADAPTER

R191.996.130

Série : ADAPTER

SMP-MAX connecting range



The connecting range represents the maximum misalignment during connection.

The swiveling angle is the maximum possible angle of the adapter in a snap receptacle.

A blind assembly is guaranteed if radial misalignment is smaller than connecting range. Otherwise a manual lead-in is necessary.

Issue: 1107 A

In the effort to improve our products, we reserve the rights to make changes judged to be necessary.




STRAIGHT ADAPTER

R191.996.130

Série : **ADAPTER**

SMP-MAX radial and axial working range



Electrical performance is achieved when radial and axial misalignments are within their working ranges.

* Radial working range = (length of the adapter)* Sin(radial working angle).

Issue: 1107 A

In the effort to improve our products, we reserve the rights to make changes judged to

