





N FEMALE BULKHEAD - SMA FEMALE STRAIGHT - PANEL SEAL+ INTERNAL ADAPTER


PAGE 1/2 ISSUE 06-12-16K SERIES ADAPT PART NUMBER R191334000



	n	mm	
	Maxi	mini	
A	16.1	16	
В	13.7	13.6	



All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
Body	.BRASS	SHINY NICKEL
Center contact	BERYLLIUM COPPER	OR SUR SOUS COUCHE NICKEL
Outer contact		
Insulator	PTFE	
Gasket	SILICONE RUBBER	
Others parts	BERYLLIUM COPPER	SHINY NICKEL
-	-	-
-	-	-



# **Technical Data Sheet**

N FEMALE BULKHEAD - SMA FEMALE STRAIGHT - PANEL SEAL+ INTERNAL ADAPTER

PAGE <b>2/2</b>	ISSUE <b>06-12-16K</b>	SERIES ADAPT	PART NUMBER <b>R191334000</b>
-----------------	------------------------	--------------	-------------------------------

#### **PACKAGING**

Standard	Unit	Other
1	-	Contact us

# **ELECTRICAL CHARACTERISTICS**

Impedance 50 Ω Frequency 0-11 GHz **VSWR** 1.30 0.0000 x F(GHz) Maxi √F(GHz) dB Maxi Insertion loss 0.125 RF leakage - ( 101 - F(GHz)) dB Maxi Voltage rating 500 Veff Maxi Dielectric withstanding voltage 1000 Veff mini 5000

 $M\Omega$  mini

### **MECHANICAL CHARACTERISTICS**

Center contact retention N mini Axial force - Mating End \*18 \*18 Axial force - Opposite end N mini Torque NA N.cm mini

Recommended torque

Insulation resistance

Mating 0 N.cm **SMA** 0 N.cm 0 N.cm Panel nut 500 N.cm

Mating life 500 Cycles mini 34,3200 Weight g

### **ENVIRONMENTAL**

Operating -55/+155 °C Hermetic seal Panel leakage NA Atm.cm3/s IP67

### **SPECIFICATION**

# OTHER CHARACTERISTICS

\* out of SMA CDC.