



## **MATERIAL:**

BODY, & INSERT:	STAINLESS STEEL PER AMS-5640, ALLOY UNS S30300, TYPE 1; OR ASTM A582 TYPE 303, COND. A	•	2X 2-56	UNC-2B	
CONTACT:	BERYLLIUM COPPER PER ASTM B196, ALLOY No. UNS C17300, TD04			285 MIN[7.24	
BEAD:	ULTEM 1000 PER ASTM D5205	∣ .420±.002 [10.67±0.05]		A	
SCREWS:	MCMASTER 91400A052				
FINISH:			.2	10±.002[ <sup>.</sup> 5.33± 	
BODY & INSERT:	PASSIVATED PER AMS-2700				
CONTACT:	GOLD PER ASTM B488, TYPE II, CODE C, CLASS 0.76, OVER NICKEL	RECOMMI	MMENDED MOUNTING HOLE		
	PER AMS-QQ-N-290, CLASS 1, .00005" MIN.	MATERIAL: SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' ±15'	UNLESS OTHE	
		FINISH: SEE NOTES	X*X' ±15 DECIMAL: .X ±.030 .XX ±.010 .XXX ±.005	1) ALL DIMENSIONS ARE IN 2) ALL DIMENSIONS ARE A 3) BREAK CORNERS & EDG 4) CHAM. 1ST & LAST THRE 5) SURFACE ROUGHNESS	
PERFORMANCE:		SURFACE AREA: N/A	.XXX ±.005 5) SURFACE ROUGHNE 6) DIA : 5 ON COMMON C INTERPRET DIMENSIONS AND TOLERANCES 7) REMOVE ALL BURRS PER ASME Y14.5M - 1994 7) REMOVE ALL BURRS		
IMPEDANCE: FREQ. RANGE:	50 OHMS DC TO 40.0 GHz.	PROPRIETARY THE INFORMATION CONTAINED IN THIS DRAWING	THIRD ANGLE PROJECTION DRAWN:		
		IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF		CHECKED:	
		SV MICROWAVE, INC IS PROHIBITED.		APPROVED:	

	REVISION HISTORY					
REV	DESCRIPTION	DATE	APPROVED			
-	NRN 45912	05/21				
			SEE PDM			







24 MIN]

3±0.05

Amphenol THERWISE SPECIFIED RE IN INCHES [MILLIMETERS] RE AFTER PLATING. § EDGES.005 R. MAX. THREADS. IESS 63₀MIL-STD-10. ◊ CENTERS TO BE CONCENTRIC TITLE: 2.92mm FEMALE TO 2.92mm FEMALE STRAIGHT 2 HOLE FLANGE ADAPTER JLP 05/17/21 SIZE DWG. NO. 1115-6128 SEE PDM SEE PDM SHEET 1 OF 1 SCALE: 5.5:1