





SMA ATTENUATOR 3 DB 12.4 GHZ 2W

PAGE 1/2 ISSUE 24-08-15E SERIES ATTENUATOR PART NUMBER R411803119







All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
Body Male center contact	STAINLESS STEEL BERYLLIUM COPPER	PASSIVATED GOLD 2 OVER NICKEL 2
Female center contact Outer contact Insulator	BERYLLIUM COPPER - PTFE	GOLD 1.3 OVER NICKEL2 -
Gasket Substrate	SILICONE RUBBER ALUMINA	
Resistor Others parts	THIN FILM	-





SMA ATTENUATOR 3 DB 12.4 GHZ 2W

PAGE 2/2	ISSUE 24-08-15E	SERIES ATTENUATOR	PART NUMBER R411803119
-----------------	------------------------	----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 4	4 - 8	8 - 12.4
V.S.W.R (≤)	1.20	1.25	1.30
Deviation(±dB)	0.30	0.40	0.50

Operating Frequency Range	DC - 12.4	GHz
Impedance	50	Ω
Nominal Attenuation	3	dB
Peak power at 25°C (1µs, 1‰)	100	W
Average power at 25°C	2	W (Free Air Cooled)
		W (Conduction Cooled)


MECHANICAL CHARACTERISTICS

Connectors	SMA	Male Female	MIL-C 39012
Weight	4,7300 g		

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55/+125	°C
Storage temperature range	-55/+125	°C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS