



MBRF30150CT THRU MBRF30200CT

Reverse Voltage - 150 to 200 Volts Forward Current - 30.0 Ampere


SCHOTTKY BARRIER RECTIFIER

Features

- ◆ The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- ◆ Construction utilizes void-free molded plastic technique
- ◆ Low reverse leakage
- ◆ High forward surge current capability
- ◆ High temperature soldering guaranteed: 250°C, 0.25" (6.35mm) from case for 10 seconds

Mechanical Data

Case : JEDEC ITO-220AB Molded plastic body
Terminals : Solder plated, solderable per MIL-STD-750, Method 2026
Polarity : Polarity symbol marking on body
Mounting Position : Any
Weight : 0.080 ounce, 2.24 grams



Dimensions in inches and (millimeters)

Maximum Ratings And Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

Parameter	SYMBOLS	MDD MBRF 30150CT	MDD MBRF 30200CT	UNITS
Marking Code				
Maximum repetitive peak reverse voltage	V_{RRM}	150	200	V
Maximum RMS voltage	V_{RMS}	135	140	V
Maximum DC blocking voltage	V_{DC}	150	200	V
Maximum average forward rectified current (see fig. 1)	$I_{(AV)}$	30.0		A
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I_{FSM}	300		A
Maximum instantaneous forward voltage at 15.0A	V_F	0.95		V
Maximum DC reverse current at rated DC blocking voltage $T_A=25^\circ\text{C}$ $T_A=100^\circ\text{C}$	I_R	0.2 50.0		mA
Typical thermal resistance (NOTE 2)	$R_{\theta Jc}$	1.5		$^\circ\text{C}/\text{W}$
Operating junction temperature range	T_J	-55 to +150		$^\circ\text{C}$
storage temperature range	T_{STG}	-55 to +150		$^\circ\text{C}$

Note: 1. Measured at 1MHz and applied reverse voltage of 4.0V D.C.

2. Thermal resistance from junction to case.



MBRF30150CT THRU MBRF30200CT

Reverse Voltage - 150 to 200 Volts Forward Current - 30.0 Ampere

Ratings And Characteristic Curves

FIG.1 TYPICAL FORWARD CHARACTERISTICS




FIG.2 FORWARD DERATING CURVE






FIG.3 TYPICAL REVERSE CHARACTERISTICS



The curve above is for reference only.