





Specifications:  
 规格:  
 Voltage rating:400V AC/DC  
 额定电压: 400V AC/DC  
 Current rating:10A AC/DC  
 额定电流: 10A AC/DC  
 Withstanding voltage:1800V AC/minute  
 耐受电压: 1800V AC/分钟  
 Temperature range:-40°C~+105°C  
 温度范围: -40°C~+105°C  
 Insulation resistance:100MΩ min  
 绝缘电阻: 100MΩ Min  
 Contact resistance:10mΩ Max  
 接触电阻: 10mΩ Max








X2513 W R -XX X S - LP SN

① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:R-Stright 90°
- 4.Row No.Pin No:XX-02~08P
- 5.Specal No:A-A Key(Black);B-B Key(Natural)
- 6.Specal No:S-With Positioning Column
- 7.Material:LP-LCP 94V-0
- 8.Plating Category:SN-Bright Tin Plating

Poles	Dimensions(mm)	
	A	B
02	5.94	2.50
03	8.44	5.00
04	10.94	7.50
05	13.44	10.00
06	15.94	12.50
07	18.44	15.00
08	20.94	17.50



X2513WR-XXXS-LPSN	LCP	Brass	X2513H
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: 2.50mm Crimp Style Connector
DWN		VIEW:	PART NO.: X2513WR-XXXS-LPSN
CHKD		UNIT: mm/in	DWG NO.: X-X2513WR-XXXS-LPSN
APPD		SIZE: A4	

MARK	DESCRIPTION	DATE	REVISED	APPROVED	ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
					L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO., LIMITED