






R1



R2



Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-40℃~+105℃

温度范围: -40℃~+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

Material:PA9T

材质: PA9T

Plating Category:1U"Gold

镀层: 1U"Gold

Reflow soldering temperature:260±5℃, 10S

回流焊温度: 260±5℃, 10S

X4612 W V S - XX I - C40 D44 - E60 X
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩

- 1.Series No.
- 2.Category:W-Water
- 3.Welding Board Angle:V-Stright 180°
- 4.Welding Way:S-SMT
- 5.Row No -Pin No:XX-02P-40P
- 6.Plastic height: l=2.0mm
- 7.Pin length: C=4.0mm
- 8.Pin Pitch:D=4.4mm
- 9.Pin length:E=6.0mm
- 10.Type:X-R1 ; R2

X4612WVS-XXI-C40D44-E60X	PA9T	Brass	1U"Gold	X4611F
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Female

DSND	SCALE: N/A	MODEL TYPE: 2.0 BTB Connector
DWN	VIEW:	PART NO.: X4612WVS-XXI-C40D44-E60X
CHKD	UNIT: mm/in	DWG NO.: X-X4612WVS-XXI-C40D44-E60X
APPD	SIZE: A4	WEIGHT
		SHEET
		REVISIC
		1/1
		A0



XKB INDUSTRIAL PRECISION CO.,LIMITED

广东星坤科技股份有限公司

Δx	日期
Δx	日期
Δx	日期
MARK	DESCRIPTION

文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5