


ELECTRICAL: INSULATOR RESISTANCE: WORKING VOLTAGE: OPERATING TEMPERATURE: POWER CONTACT RESISTANCE: SIGNAL CONTACT RESISTANCE: POWER CONTACT AMPERAGE: SIGNAL CONTACT AMPERAGE:	5 GOhms MIN. 250V -55°C TO +125°C 2.0 mOhms MAX. 10 mOhms MAX. SEE P/N KEY 5 AMPS
MECHANICAL:	
CONTACT INSERTION FORCE:	4.5 Kg MAX.
CONTACT SEPARATION FORCE:	0.3 Kg MIN.
MATERIALS:	
CONTACTS:	COPPER ALLOY, GOLD FLASH
INSULATOR:	PBT UL94V-0 RATED
	230°C PROCESS TEMP.
SHELL:	NICKEL PLATED STEEL
BRACKET:	NICKEL PLATED STEEL
BOARD LOCK:	NICKEL PLATED BRASS



SEE SHEET 2 FOR CONTACT & BRACKET DIMENSION DETAILS

684M9W4103LYYY

46 = 40 AMP POWER // #4-40 BRACKET // STANDARD PCB TAILS — 62 = 40 AMP POWER // #4-40 BRACKET // 2.22mm PCB TAILS

1 = GOLD FLASH -



