


## Features

- General rectification
- Low  $V_F$ ; Low  $I_R$
- High reliability



SOD123

PIN	DESCRIPTION
1	Cathode
2	Anode



## Applications

- surface mount schottky barrier rectifier

## Ordering Information

- Shipping Qty:3000/7inch Tape& Reel

## Marking: B2.X

“B2” is part number, fixed

“x” is internal code

## Absolute Maximum Ratings ( $T_A=25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Value	Unit
Peak Repetitive Reverse Voltage	$V_{RRM}$	20	V
RMS Reverse Voltage	$V_{RMS}$	14	V
Maximum Average Forward Output Current	$I_{F(AV)}$	0.5	A
Peak Forward Surge Current (8.3ms single half sine-wave)	$I_{FSM}$	5.5	A


## Thermal Characteristics

Parameter	Symbol	Value	Unit
Power Dissipation	$P_D$	500	mW
Operating junction Temperature	$T_J$	150	$^\circ\text{C}$
Storage Temperature Range	$T_{STG}$	-55 ~ +150	$^\circ\text{C}$


## Electrical Characteristics ( $T_A=25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Test Condition	Min.	Typ.	Max.	Unit
Forward Voltage	$V_F$	$I_F = 0.1\text{A}$	-	-	0.375	V
		$I_F = 0.5\text{A}$	-	-	0.44	
Maximum Peak Reverse Current	$I_R$	$V_R = 20\text{V}$	-	-	20	$\mu\text{A}$

**Ratings and Characteristic Curves** (@  $T_A = 25^\circ\text{C}$  unless otherwise specified)




**Fig. 1 Forward Characteristics**



**Fig. 2 Typical Reverse Characteristic**

**Outline Drawing - SOD123 (unit: mm)**



SOD-123		
Dim	Min	Max
A	1.45	1.75
B	2.55	2.85
C	1.00	1.30
D	0.50	0.60
E	0.25	0.45
H	0.02	0.10
J	0.05	0.15
K	3.55	3.85

**Mounting Pad Layout-SOD123 (unit: mm)**

