



Spec No.: DS30-2000-320 Effective Date: 06/05/2010

Revision: B

LITE-ON DCC

RELEASE

BNS-OD-FC001/A4

Property of Lite-On Only

FEATURES

- *0.52 inch (13.2 mm) DIGIT HEIGHT.
- *CONTINUOUS UNIFORM SEGMENTS.
- *LOW POWER REQUIREMENT.
- *EXCELLENT CHARACTERS APPEARANCE.
- *HIGH BRIGHTNESS & HIGH CONTRAST.
- *WIDE VIEWING ANGLE.
- * SOLID STATE RELIABILITY.
- *CATEGORIZED FOR LUMINOUS INTENSITY.

DESCRIPTION

The LTS-546AJD is a 0.52 inch (13.2 mm) height single digit display. This device utilizes AlInGaP Hyper red LED chips, which are made from AlInGaP on a non-transparent GaAs substrate, and has a gray face and white segments.


DEVICE

PART NO.	DESCRIPTION			
AlInGaP Hyper RED	Common Anode			
LTS-546AJD	Rt. Hand decimal			

PART NO.: LTS-546AJD	PAGE:	1 of 5	
----------------------	-------	--------	--


Property of Lite-On Only

PACKAGE DIMENSIONS



NOTES: All dimensions are in millimeters. Tolerances are \pm 0.25-mm (0.01") unless otherwise noted.

INTERNAL CIRCUIT DIAGRAM



PART NO.: LTS-546AJD PAGE: 2 of 5

Property of Lite-On Only

PIN CONNECTION

No.	CONNECTION
1	CATHODE E
2	CATHODE D
3	COMMON ANODE
4	CATHODE C
5	CATHODE D.P.
6	CATHODE B
7	CATHODE A
8	COMMON ANODE
9	CATHODE F
10	CATHODE G

PART NO.: LTS-546AJD PAGE: 3 of 5

Property of Lite-On Only

ABSOLUTE MAXIMUM RATING AT Ta=25°C

PARAMETER	MAXIMUM RATING	UNIT		
Power Dissipation Per Segment	70	mW		
Peak Forward Current Per Segment	00			
(1/10 Duty Cycle, 0.1ms Pulse Width)	90	mA		
Continuous Forward Current Per Segment	25	mA		
Derating Linear From 25 ^o C Per Segment	0.33	mA/ ⁰ C		
Reverse Voltage Per Segment	5	V		
Operating Temperature Range	-35° C to $+85^{\circ}$ C			
Storage Temperature Range	-35^{0} C to $+85^{0}$ C			
Solder Temperature 1/16 inch Below Seating Plane for 3 Seconds at 260 ^o C				

ELECTRICAL / OPTICAL CHARACTERISTICS AT Ta=25°C

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	Iv	320	808		μcd	I _F =1mA
			10500			I _F =10mA
Peak Emission Wavelength	λр		650		nm	I _F =20mA
Spectral Line Half-Width	Δλ		20		nm	I _F =20mA
Dominant Wavelength	λd		639		nm	I _F =20mA
Forward Voltage Per Segment	VF		2.1	2.6	V	I _F =20mA
Reverse Current Per Segment	IR			100	μΑ	V _R =5V
Luminous Intensity Matching Ratio	Iv-m			2:1		I _F =10mA


Note: Luminous intensity is measured with a light sensor and filter combination that approximates the CIE (Commision Internationale De L'Eclariage) eye-response curve.


PART NO.: LTS-546AJD PAGE: 4 of 5


Property of Lite-On Only


TYPICAL ELECTRICAL / OPTICAL CHARACTERISTIC CURVES

(25°C Ambient Temperature Unless Otherwise Noted)









JD Relative Lumi (Normalized T Forward Current (IF)-mA
Fig4. RELATIVE LUMINOUS INTENSITY

VS. FORWARD CURRENT




Fig6. MAX. PEAK CURRENT VS.
DUTY CYCLE %
(REFRESH RATE 1KHz)

NOTE: JD=AlInGaP HYPER RED

PART NO.: LTS-546AJD PAGE: 5 of 5