

SOD-523 Plastic-Encapsulate ESD Protection Diodes

Features


- Low leakage current
- SOD-523 surface mount package
- IEC 61000-4-2 (ESD Air): $\pm 30\text{kV}$
- IEC 61000-4-2 (ESD Contact): $\pm 30\text{kV}$
- IEC 61000-4-5 (Lightning 8/20 μs): 15A

Reverse Working Voltage
12V Max.
Normal capacitance
90pF(Max.)

Applications

- Cellular Handsets and Accessories
- Personal Digital Assistants
- Notebook computers
- Notebooks and Handhelds
- Peripherals, Audio Players
- Industrial Equipment

Function Diagram




Maximum Ratings (Ta=25°C Unless otherwise specified)

| SYMBOL | PARAMETER | CONDITIONS | VALUE | UNIT |
|-----------|-------------------------------------|----------------------------------|-------------|------|
| V_{ESD} | Electrostatic Discharge Voltage | ESD per IEC 61000-4-2(Air) | ± 30 | kV |
| | | ESD per IEC 61000-4-2(Contact) | ± 30 | kV |
| P_{PP} | Peak Pulse Power | $t_p = 8/20 \mu\text{s}$ | 360 | W |
| I_{PP} | Rated Peak Pulse Current | $t_p = 8/20 \mu\text{s}$ | 15 | A |
| T_J | Operating JunctionTemperature Range | — | -55 to +125 | °C |
| T_{STG} | Operating JunctionTemperature Range | — | -55 to +150 | °C |

Electrical Parameter





| SYMBOL | PARAMETER |
|-----------|---|
| V_C | Clamping Voltage @ I_{PP} |
| V_{BR} | Breakdown Voltage @ I_T |
| I_{PP} | Peak Pulse Current |
| I_T | Test Current |
| I_R | Reverse Leakage Current @ VRWM |
| V_{RWM} | Peak Reverse Working Voltage |
| P_{PP} | Peak Pulse Power Dissipation |
| C_J | Junction Capacitance @ $V_R=0\text{V}, f=1\text{MHz}$ |
| I_F | Forward Current |
| V_F | Forward Voltage @ I_F |



● Electrical Characteristics (Ta=25°C Unless otherwise specified)

| PARAMETER | SYMBOL | CONDITION | Min | Typ | Max | UNIT |
|------------------------------|------------------|--|------|-----|-----|------|
| Peak Reverse Working Voltage | V _{RWM} | T _a =25°C | — | — | 12 | V |
| Breakdown Voltage | V _{BR} | I _R =1mA, T _a =25°C | 13.2 | — | 16 | V |
| Reverse Leakage Current | I _R | V _R =12V, T _a =25°C | — | — | 0.1 | μA |
| Clamping Voltage | V _C | I _{PP} =5A, t _p =8/20μs | — | — | 16 | V |
| | | I _{PP} =15A, t _p =8/20μs | — | — | 24 | |
| Junction Capacitance | C _J | V _R =0V, f=1MHz | — | — | 90 | pF |


● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)




● Ordering Information

| PREFERRED P/N | PACKAGE CODE | PACKAGE | SIZE(mm) | DELIVERY MODE | MPQ(PCS) |
|---------------|--------------|---------|-----------------|---------------|----------|
| H15VND5U | R1 | SOD-523 | 0.30×0.80×0.115 | 7" REEL | 3000 |
| | R1H | SOD-523 | 0.30×0.80×0.115 | 7" REEL | 8000 |

● Recommended Soldering Conditions



● Package Outline Dimensions (SOD-523)



| Symbol | Dimensions | | | |
|--------|-------------|------|--------|-------|
| | Millimeters | | Inches | |
| | Min | Max | Min | Max |
| A | 1.10 | 1.30 | 0.044 | 0.052 |
| B | 0.25 | 0.35 | 0.01 | 0.014 |
| C | 1.50 | 1.70 | 0.06 | 0.068 |
| D | 0.50 | 0.70 | 0.02 | 0.028 |
| E | 0.70 | 0.90 | 0.028 | 0.036 |
| F | 0.05 | 0.20 | 0.002 | 0.008 |

● Suggested Pad Layout

