THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

												_				
		DIMENSIONS – in [mm]								INSTALLA			— w —			
		ART #	STUD SIZE	A ±	.03 [0,8]	$W\pm \begin{array}{c} .01\\ [0,3]\end{array}$	$C \pm rac{.02}{[0,51]}$	M ± ^{.03} [0,8]	H± .01 [0,3]	CT-520 CT-1525 (A PO	CKET)				H DIA	
	PN	22–4F	#2	.67 [[.]	17,02]	.20 [5,08]	.21 [5,33]	.57 [14,49]	.12 [3,05]	CT-2500 (CT-2	525CH: A PKT)				TERMIN	JAL
В	PN	22–6F	#6	.77 [19,56]	.25 [6,35]	.26 [6,60]	.63 [16,00]	.15 [3,81]						C RAD	B
47)	
Α											F	ORK TER	MINAL, N #26-23 control	2 AWG	SULATED	A
												N41235BA/08				
											DATASET FILE NAME N41235BA_DC/08			MATERIAL	TAN DUI	
											UNLESS O DIMENSIONAL	TOLERANCES	HERWISE SPECIFIED, DLERANCES ARE: IN [mm]		SEE NOTES	
16		04-27-15		JHNU		ADDED CT-1525			IL FORMAT	A 41235	.XX ± .01 [.25] ANGLES ±			DRAWING	DRAWING NUMBER:	
D10100DA/16	07	04-26-13			RTFI	UPDATED DRAW		IIILE DLUUK		A 41235			PROJECTION		A41235	
D101(REV	DATE	BY	СНК	APR		DESC	RIPTION		ECN	DAW –	-	NONE		SHT 1 OF 1	А