FAIRCHILD
SEMICONDUCTOR TM

2N4400



TO-92

MMBT4400



SOT-23
Mark: 83

NPN General Purpose Amplifier

This device is designed for use as general purpose amplifiers and switches requiring collector currents to 500 mA.

Absolute Maximum Ratings*

TA = 25°C unless otherwise noted

Symbol	Parameter	Value	Units
V_{CEO}	Collector-Emitter Voltage	40	V
V_{CBO}	Collector-Base Voltage	60	V
V_{EBO}	Emitter-Base Voltage	6.0	V
I_C	Collector Current - Continuous	600	mA
T_J, T_{stg}	Operating and Storage Junction Temperature Range	-55 to +150	°C

*These ratings are limiting values above which the serviceability of any semiconductor device may be impaired.

NOTES:
1) These ratings are based on a maximum junction temperature of 150 degrees C.
2) These are steady state limits. The factory should be consulted on applications involving pulsed or low duty cycle operations.

Thermal Characteristics

TA = 25°C unless otherwise noted

Symbol	Characteristic	Max		Units
		2N4400	*MMBT4400	
P_D	Total Device Dissipation Derate above 25°C	625 5.0	350 2.8	mW mW/°C
$R_{\theta JC}$	Thermal Resistance, Junction to Case	83.3		°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient	200	357	°C/W

NPN General Purpose Amplifier
(continued)

Electrical Characteristics
TA = 25°C unless otherwise noted

Symbol	Parameter	Test Conditions	Min	Max	Units
OFF CHARACTERISTICS					
$V_{(BR)CEO}$	Collector-Emitter Breakdown Voltage*	I_C = 1.0 mA, I_B = 0	40		V
$V_{(BR)CBO}$	Collector-Base Breakdown Voltage	I_C = 100 µA, I_E = 0	60		V
$V_{(BR)EBO}$	Emitter-Base Breakdown Voltage	I_E = 100 µA, I_C = 0	6.0		V
I_{CEX}	Collector Cutoff Current	V_{CE} = 35 V, V_{EB} = 0.4 V		0.1	µA
I_{BL}	Emitter Cutoff Current	V_{CE} = 35 V, V_{EB} = 0.4 V		0.1	µA
ON CHARACTERISTICS*					
h_{FE}	DC Current Gain	V_{CE} = 1.0 V, I_C = 1.0 mA V_{CE} = 1.0 V, I_C = 10 mA V_{CE} = 1.0 V, I_C = 150 mA V_{CE} = 2.0 V, I_C = 500 mA	20 40 50 20	 150 	
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage	I_C = 150 mA, I_B =15 mA I_C = 500 mA, I_B = 50 mA		0.40 0.75	V V
$V_{BE(sat)}$	Base-Emitter Saturation Voltage	I_C = 150 mA, I_B =15 mA I_C = 500 mA, I_B = 50 mA	0.75	0.95 1.2	V V
SMALL SIGNAL CHARACTERISTICS					
C_{ob}	Output Capacitance	V_{CB} = 5.0 V, f = 140 kHz		6.5	pF
C_{ib}	Input Capacitance	V_{EB} = 0.5 V, f = 140 kHz		30	pF
h_{fe}	Small-Signal Current Gain	I_C = 20 mA, V_{CE} = 10 V, f = 100 MHz	2.0		
h_{fe}	Small-Signal Current Gain	V_{CE} = 10 V, I_C = 1.0 mA, f = 1.0 kHz	20	250	
h_{ie}	Input Impedance		0.5	7.5	KΩ
h_{re}	Voltage Feedback Ratio		0.1	8.0	x 10^{-4}
h_{oe}	Output Admittance		1.0	30	µmhos
SWITCHING CHARACTERISTICS					
t_d	Delay Time	V_{CC} = 30 V, I_C = 150 mA, I_{B1} = 15 mA ,V_{EB} = 2 V		15	ns
t_r	Rise Time			20	ns
t_s	Storage Time	V_{CC} = 30 V, I_C = 150 mA, I_{B1} = I_{B2} = 15 mA		225	ns
t_f	Fall Time			30	ns

*Pulse Test: Pulse Width £ 300 ms, Duty Cycle £ 2.0%

NPN General Purpose Amplifier

(continued)

Typical Characteristics

Typical Pulsed Current Gain vs Collector Current



Collector-Emitter Saturation Voltage vs Collector Current



Base-Emitter Saturation Voltage vs Collector Current



Base-Emitter ON Voltage vs Collector Current



Collector-Cutoff Current vs Ambient Temperature



Emitter Transition and Output Capacitance vs Reverse Bias Voltage



Typical Characteristics (continued)

Turn On and Turn Off Times vs Collector Current



Switching Times vs Collector Current



Power Dissipation vs Ambient Temperature



NPN General Purpose Amplifier

(continued)

Typical Common Emitter Characteristics (f = 1.0kHz)







Test Circuits



FIGURE 1: Saturated Turn-On Switching Timer



FIGURE 2: Saturated Turn-Off Switching Time

TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

ACEx™
Bottomless™
CoolFET™
CROSSVOLT™
DOME™
E^2CMOS^{TM}
EnSigna™
FACT™
FACT Quiet Series™
FAST®
FASTr™
GlobalOptoisolator™
GTO™
HiSeC™
ISOPLANAR™
MICROWIRE™
OPTOLOGIC™
OPTOPLANAR™
PACMAN™
POP™
PowerTrench®
QFET™
QS™
QT Optoelectronics™
Quiet Series™
SILENT SWITCHER®
SMART START™
SuperSOT™-3
SuperSOT™-6
SuperSOT™-8
SyncFET™
TinyLogic™
UHC™
VCX™

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.
As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

PRODUCT STATUS DEFINITIONS

Definition of Terms

Datasheet Identification	Product Status	Definition
Advance Information	Formative or In Design	This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
No Identification Needed	Full Production	This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
Obsolete	Not In Production	This datasheet contains specifications on a product that has been discontinued by Fairchild semiconductor. The datasheet is printed for reference information only.

2N4400

NPN General Purpose Amplifier

Contents

BUY

Datasheet

Download this datasheet

e-mail this datasheet

This page

Print version

Related Links

- Request samples
- How to order products
- Product Change Notices (PCNs)
- Support
- Sales support
- Quality and reliability
- Design center

General description

This device is designed for use as general purpose amplifiers and switches requiring collector currents to 500 mA.

back to top

Product status/pricing/packaging

BUY

Product	Product status	Pb-free Status	Pricing*	Package type	Leads	Packing method	Package Marking Convention**
2N4400BU	Full Production	Full Production	$0.026	TO-92	3	BULK	Line 1: 2N Line 2: 4400 Line 3: -&3
2N4400TA	Full Production	Full Production	$0.026	TO-92	3	AMMO	Line 1: 2N Line 2: 4400 Line 3: -&3
2N4400TAR	Full Production	Full Production	$0.026	TO-92	3	AMMO	Line 1: 2N Line 2: 4400 Line 3: -&3
2N4400TF	Full Production		$0.026	TO-92	3	TAPE REEL	Line 1: 2N Line 2: 4400 Line 3: -&3

		Full Production					
2N4400TFR	Full Production	Full Production	$0.026	TO-92	3	TAPE REEL	Line 1: 2N Line 2: 4400 Line 3: -&3
2N4400_D81Z	Full Production	Full Production	N/A	TO-92	3	TAPE REEL	Line 1: **$Y** (Fairchild logo) &**Z** (Asm. Plant Code) &**3** (3-Digit Date Code) Line 2: 2N Line 3: 4400

* Fairchild 1,000 piece Budgetary Pricing
** A sample button will appear if the part is available through Fairchild's on-line samples program. If there is no sample button, please contact a Fairchild distributor to obtain samples

Indicates product with Pb-free second-level interconnect. For more information click here.

Package marking information for product 2N4400 is available. Click here for more information .

back to top

Models

Package & leads	Condition	Temperature range	Software version	Revision date
PSPICE				
TO-92-3	Electrical	25°C	N/A	N/A

back to top

Qualification Support

Click on a product for detailed qualification data

Product
2N4400BU
2N4400TA
2N4400TAR
2N4400TF
2N4400TFR

2N4400_D81Z

back to top