

# BC556B, BC557, A, B, C, BC558B, C



ON Semiconductor™

<http://onsemi.com>

## Amplifier Transistors


PNP Silicon

### MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Collector-Emitter Voltage BC556 BC557 BC558	$V_{CEO}$	-65 -45 -30	Vdc
Collector-Base Voltage BC556 BC557 BC558	$V_{CBO}$	-80 -50 -30	Vdc
Emitter-Base Voltage	$V_{EBO}$	-5.0	Vdc
Collector Current – Continuous – Peak	$I_C$ $I_{CM}$	-100 -200	mAdc
Base Current – Peak	$I_{BM}$	-200	mAdc
Total Device Dissipation @ $T_A = 25^\circ\text{C}$ Derate above $25^\circ\text{C}$	$P_D$	625 5.0	mW mW/ $^\circ\text{C}$
Total Device Dissipation @ $T_C = 25^\circ\text{C}$ Derate above $25^\circ\text{C}$	$P_D$	1.5 12	Watts mW/ $^\circ\text{C}$
Operating and Storage Junction Temperature Range	$T_J, T_{stg}$	-55 to +150	$^\circ\text{C}$

### THERMAL CHARACTERISTICS

Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction to Ambient	$R_{\theta JA}$	200	$^\circ\text{C}/\text{W}$
Thermal Resistance, Junction to Case	$R_{\theta JC}$	83.3	$^\circ\text{C}/\text{W}$



### ORDERING INFORMATION

Device	Package	Shipping
BC556B	TO-92	5000 Units/Box
BC556BRL1	TO-92	2000/Tape & Reel
BC556BZL1	TO-92	2000/Ammo Pack
BC557	TO-92	5000 Units/Box
BC557ZL1	TO-92	2000/Ammo Pack
BC557A	TO-92	5000 Units/Box
BC557AZL1	TO-92	2000/Ammo Pack
BC557B	TO-92	5000 Units/Box
BC557BRL1	TO-92	2000/Tape & Reel
BC557BZL1	TO-92	2000/Ammo Pack
BC557C	TO-92	5000 Units/Box
BC557CZL1	TO-92	2000/Ammo Pack
BC558B	TO-92	5000 Units/Box
BC558BRL	TO-92	2000/Tape & Reel
BC558BRL1	TO-92	2000/Tape & Reel
BC558BZL1	TO-92	2000/Ammo Pack
BC558C	TO-92	5000 Units/Box
BC558CRL1	TO-92	2000/Tape & Reel
BC558ZL1	TO-92	2000/Ammo Pack
BC558CZL1	TO-92	2000/Ammo Pack

## BC556B, BC557, A, B, C, BC558B, C

### ELECTRICAL CHARACTERISTICS ( $T_A = 25^\circ\text{C}$ unless otherwise noted)

Characteristic		Symbol	Min	Typ	Max	Unit
<b>OFF CHARACTERISTICS</b>						
Collector–Emitter Breakdown Voltage ( $I_C = -2.0\text{ mA}$ , $I_B = 0$ )	BC556	$V_{(BR)CEO}$	-65	-	-	V
	BC557		-45	-	-	
	BC558		-30	-	-	
Collector–Base Breakdown Voltage ( $I_C = -100\ \mu\text{A}$ )	BC556	$V_{(BR)CBO}$	-80	-	-	V
	BC557		-50	-	-	
	BC558		-30	-	-	
Emitter–Base Breakdown Voltage ( $I_E = -100\ \mu\text{A}$ , $I_C = 0$ )	BC556	$V_{(BR)EBO}$	-5.0	-	-	V
	BC557		-5.0	-	-	
	BC558		-5.0	-	-	
Collector–Emitter Leakage Current ( $V_{CES} = -40\text{ V}$ ) ( $V_{CES} = -20\text{ V}$ )  ( $V_{CES} = -20\text{ V}$ , $T_A = 125^\circ\text{C}$ )	BC556	$I_{CES}$	-	-2.0	-100	nA
	BC557		-	-2.0	-100	
	BC558		-	-2.0	-100	
	BC556		-	-	-4.0	$\mu\text{A}$
	BC557		-	-	-4.0	
	BC558		-	-	-4.0	

# BC556B, BC557, A, B, C, BC558B, C

## ELECTRICAL CHARACTERISTICS (T<sub>A</sub> = 25°C unless otherwise noted)

Characteristic	Symbol	Min	Typ	Max	Unit	
<b>ON CHARACTERISTICS</b>						
DC Current Gain (I <sub>C</sub> = -10 μAdc, V <sub>CE</sub> = -5.0 V)	h <sub>FE</sub>	A Series Device	-	90	-	-
		B Series Devices	-	150	-	-
		C Series Devices	-	270	-	-
(I <sub>C</sub> = -2.0 mAdc, V <sub>CE</sub> = -5.0 V)	h <sub>FE</sub>	BC557	120	-	800	-
		A Series Device	120	170	220	-
		B Series Devices	180	290	460	-
	C Series Devices	420	500	800	-	-
(I <sub>C</sub> = -100 mAdc, V <sub>CE</sub> = -5.0 V)	h <sub>FE</sub>	A Series Device	-	120	-	-
		B Series Devices	-	180	-	-
		C Series Devices	-	300	-	-
Collector-Emitter Saturation Voltage (I <sub>C</sub> = -10 mAdc, I <sub>B</sub> = -0.5 mAdc) (I <sub>C</sub> = -10 mAdc, I <sub>B</sub> = see Note 1) (I <sub>C</sub> = -100 mAdc, I <sub>B</sub> = -5.0 mAdc)	V <sub>CE(sat)</sub>	-	-0.075	-0.3	V	
		-	-0.3	-0.6		
		-	-0.25	-0.65		
Base-Emitter Saturation Voltage (I <sub>C</sub> = -10 mAdc, I <sub>B</sub> = -0.5 mAdc) (I <sub>C</sub> = -100 mAdc, I <sub>B</sub> = -5.0 mAdc)	V <sub>BE(sat)</sub>	-	-0.7	-	V	
		-	-1.0	-		
Base-Emitter On Voltage (I <sub>C</sub> = -2.0 mAdc, V <sub>CE</sub> = -5.0 Vdc) (I <sub>C</sub> = -10 mAdc, V <sub>CE</sub> = -5.0 Vdc)	V <sub>BE(on)</sub>	-0.55	-0.62	-0.7	V	
		-	-0.7	-0.82		

## SMALL-SIGNAL CHARACTERISTICS

Current-Gain – Bandwidth Product (I <sub>C</sub> = -10 mA, V <sub>CE</sub> = -5.0 V, f = 100 MHz)	f <sub>T</sub>	-	280	-	MHz
		-	320	-	
		-	360	-	
Output Capacitance (V <sub>CB</sub> = -10 V, I <sub>C</sub> = 0, f = 1.0 MHz)	C <sub>ob</sub>	-	3.0	6.0	pF
Noise Figure (I <sub>C</sub> = -0.2 mAdc, V <sub>CE</sub> = -5.0 V, R <sub>S</sub> = 2.0 kΩ, f = 1.0 kHz, Δf = 200 Hz)	NF	-	2.0	10	dB
		-	2.0	10	
		-	2.0	10	
Small-Signal Current Gain (I <sub>C</sub> = -2.0 mAdc, V <sub>CE</sub> = 5.0 V, f = 1.0 kHz)	h <sub>fe</sub>	125	-	900	-
		125	-	260	
		240	-	500	
		450	-	900	

Note 1: I<sub>C</sub> = -10 mAdc on the constant base current characteristics, which yields the point I<sub>C</sub> = -11 mAdc, V<sub>CE</sub> = -1.0 V.

# BC556B, BC557, A, B, C, BC558B, C

## BC557/BC558




Figure 1. Normalized DC Current Gain




Figure 2. "Saturation" and "On" Voltages




Figure 3. Collector Saturation Region




Figure 4. Base-Emitter Temperature Coefficient




Figure 5. Capacitances




Figure 6. Current-Gain - Bandwidth Product

# BC556B, BC557, A, B, C, BC558B, C

## BC556




Figure 7. DC Current Gain




Figure 8. "On" Voltage




Figure 9. Collector Saturation Region




Figure 10. Base-Emitter Temperature Coefficient




Figure 11. Capacitance




Figure 12. Current-Gain - Bandwidth Product

# BC556B, BC557, A, B, C, BC558B, C




Figure 13. Thermal Response




Figure 14. Active Region – Safe Operating Area



The safe operating area curves indicate  $I_C$ - $V_{CE}$  limits of the transistor that must be observed for reliable operation. Collector load lines for specific circuits must fall below the limits indicated by the applicable curve.

The data of Figure 14 is based upon  $T_{J(pk)} = 150^\circ\text{C}$ ;  $T_C$  or  $T_A$  is variable depending upon conditions. Pulse curves are valid for duty cycles to 10% provided  $T_{J(pk)} \leq 150^\circ\text{C}$ .  $T_{J(pk)}$  may be calculated from the data in Figure 13. At high case or ambient temperatures, thermal limitations will reduce the power than can be handled to values less than the limitations imposed by second breakdown.

# BC556B, BC557, A, B, C, BC558B, C

## PACKAGE DIMENSIONS

TO-92  
(TO-226)  
CASE 29-11  
ISSUE AL



### NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.
3. CONTOUR OF PACKAGE BEYOND DIMENSION R IS UNCONTROLLED.
4. LEAD DIMENSION IS UNCONTROLLED IN P AND BEYOND DIMENSION K MINIMUM.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.175	0.205	4.45	5.20
B	0.170	0.210	4.32	5.33
C	0.125	0.165	3.18	4.19
D	0.016	0.021	0.407	0.533
G	0.045	0.055	1.15	1.39
H	0.095	0.105	2.42	2.66
J	0.015	0.020	0.39	0.50
K	0.500	---	12.70	---
L	0.250	---	6.35	---
N	0.080	0.105	2.04	2.66
P	---	0.100	---	2.54
R	0.115	---	2.93	---
V	0.135	---	3.43	---

### STYLE 17:

1. COLLECTOR
2. BASE
3. EMITTER

## BC556B, BC557, A, B, C, BC558B, C

**ON Semiconductor** and  are trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer.

### PUBLICATION ORDERING INFORMATION

**Literature Fulfillment:**

Literature Distribution Center for ON Semiconductor  
P.O. Box 5163, Denver, Colorado 80217 USA  
**Phone:** 303-675-2175 or 800-344-3860 Toll Free USA/Canada  
**Fax:** 303-675-2176 or 800-344-3867 Toll Free USA/Canada  
**Email:** ONlit@hibbertco.com

**N. American Technical Support:** 800-282-9855 Toll Free USA/Canada

**JAPAN:** ON Semiconductor, Japan Customer Focus Center  
4-32-1 Nishi-Gotanda, Shinagawa-ku, Tokyo, Japan 141-0031  
**Phone:** 81-3-5740-2700  
**Email:** r14525@onsemi.com

**ON Semiconductor Website:** <http://onsemi.com>

For additional information, please contact your local Sales Representative.