




MATERIAL NO.	ENG. NO.	STUD SIZE	"S" MAX	DESCRIPTION
192030388	19203-0388	10	.212/5.38	LOOSE
192030052	B-S-137-10T	10	.212/5.38	TAPE

(E1)



PARTS ON TAPE

- NOTES:
1. MATERIAL: STEEL
 2. WIRE SIZE: 16-14 AWG (1.5-2.5 MM²)
 3. FINISH: NICKEL PLATED WITH OPTIONAL COPPER FLASH UNDERPLATING, IS ALLOWED FOR IMPROVED ADHESION.
 4. PART IS ROHS COMPLIANT.
 5. AMBIENT OPERATING TEMPERATURE UP TO 900 °F (483 °C).

(E1)

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
FUNCTIONAL SYMBOLS	FA = 0	IN/MM	SCALE	4:1	CURRENT REV DESC: REMASTERED IN ECTR AND UPDATED NOTE					
	FC = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)			EC NO: 708789					
DIVISIONAL SYMBOLS	FD = 0	4 PLACES	±	MM	±	INCH	±	DRWN: PAWANC	2022/05/10	
		3 PLACES	±		±		±	CHKD: DMYRICK	2022/06/01	
		2 PLACES	±		±		±	APPR: JMACNEIL	2022/06/02	
		1 PLACE	±		±		±	INITIAL REVISION:		
		0 PLACES	±		±		±	DRWN: DMYRICK	2005/04/06	
		ANGULAR TOL	±	°			APPR: RDEROSS	2005/04/06		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		
				B-SIZE		19203		SEE CHART		
								CUSTOMER		
								GENERAL MARKET		
								SHEET NUMBER		
								1 OF 1		