



All dimensions are in mm; tolerances according to ISO 2768 m-H

Interface

According to	P-SMP side:	Rosenberger P-SMP
	SMA side:	IEC 60169-15; EN 122110; MIL-STD-348A, Fig. 310

Documents

N/A

Material and plating

Connector parts

	Material	Plating
Center contact	CuBe	AuroDur®, gold plated
Outer contact P-SMP side	CuBe	AuroDur®, gold plated
Outer contact SMA side	Stainless steel	Passivated
Coupling nut	Stainless steel	Passivated
Dielectric	PTFE	

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG

RF_35/09.14/6.2

Electrical data

Impedance	50 Ω
Frequency	DC to 10 GHz
Return loss	≥ 38 dB, DC to 4 GHz ≥ 26 dB, 4 to 10 GHz
Insertion loss	≤ 0.05 x √f(GHz) dB, DC to 10 GHz
Insulation resistance	≥ 5 GΩ
Center contact resistance	≤ 3.0 mΩ
Outer contact resistance	≤ 2.0 mΩ
Test voltage	1000 V rms
Working voltage	480 V rms
Power handling (at 20 °C, sea level, VSWR 1.0)	≤ 200 W @ 2.2 GHz

Mechanical data

	SMA side	P-SMP side
Mating cycles	≥ 500	
if mating part is Smooth bore, Catchers mitt		≥ 1000
if mating part is Limited detent		≥ 100
if mating part is Full detent		≥ 100
Center contact captivation: axial	≥ 27 N	≥ 27 N
Engagement force:		
- Smooth bore, Catchers mitt	N/A	≤ 10 N
- Limited detent	N/A	≤ 45 N
- Full detent	N/A	≤ 68 N
Disengagement force:		
- Smooth bore, Catchers mitt	N/A	≥ 2.2 N
- Limited detent	N/A	≥ 15 N
- Full detent	N/A	≥ 25 N
Coupling test torque	≤ 1.7 Nm	N/A
Recommended torque	0.8 Nm to 1.1 Nm	N/A
Permissible angular misalignment		4°

Environmental data

Temperature range	-55°C to +155°C
Rapid change of temperature	IEC 60169-1, Sub-clause 16.4 (-55°C to +155°C)
Vibration	IEC 60068-2-64 random
Shock	IEC 60068-2-27 (half-sine)
High temperature endurance	IEC 60169-1, Sub-clause 18 (+155°C, 1000 hours)
RoHS	compliant

Weight

Weight	5.5 g/pce
--------	-----------

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

For the installation of the electrotechnical equipment, particular electrotechnical expertise is required.



Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG

RF_35/09.14/6.2

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
M. Schmid	21.11.08	Chr. Janßen	19.10.20	d00	20-1927	S. Huber-Siegl	19.10.20

Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de				Tel. : +49 8684 18-0 Email : info@rosenberger.de		Page 2 / 2	
--	--	--	--	--	--	---------------	--