



**ANATECH ELECTRONICS INC**  
RF & Microwave Filters & Products

# 70 MHz LC Band Pass Filter

Part Number: AE70B11628



## Electrical Specifications

**Center Frequency:** 70 MHz  
**Bandwidth:** 10 MHz  
**Passband Insertion Loss:** 1.2 dB Max.  
**Passband Return Loss :** 20 dB Min.  
**Rejection:** ≥ 60 dB @ 140 MHz  
**Impedance:** 50 Ohms In/Out  
**Power Handling:** 0.01 W


## Mechanical

**Mounting Method:** 2-56 Tap Holes  
**Connector Type:** SMA(F)  
**Dimensions:** 2.5" X 1.125" x 0.75"

## Environmental

**Operating Temperature:** -25°C to +70°C  
**Storage Temperature:** -75°C to +90°C  
**Shock:** 10 G. 11ms  
**Vibration:** 10 G. 5 to 200Hz

## Outline Drawing:



Tolerance: +/-0.01 inches [+/- 0.3mm]

Angles: +/- 1 Deg.

\*Tolerance as shown unless otherwise specified in the datasheet electrical specification tables above.

\*When max dimensions are called out the above tolerances do not apply as long as it is under the max call out.

DS-B11628-06172019-Rev0

70 Outwater Lane  
Garfield, NJ 07026

Phone: (973) 772-4242  
Fax : (973) 321-3941

Reference DCR: D061719-05A

Email: [sales@anatechelectronics.com](mailto:sales@anatechelectronics.com)  
Web: [www.anatechelectronics.com](http://www.anatechelectronics.com)



### Response Plot:

