



P.C.BLAYOUT



COLOR 1#  
COLOR 2#



NOTES:

- 1.RATING:12VDC20mA
- 2.CONTACT RESISTANCE:100mΩ Max
- 3.INSULATION RESISTANCE:100MΩ 250VDC FOR1MIN
- 4.DIELECTRIC STRENGTH: 250VAC (50/60Hz) FOR1MIN
- 5.LIFE TEST: 50,000 CYCLES (1Ω Max)
- 6.OPERATION FORCE:250±80g
- 7.TRAVEL: 0.25±0.1mm

TOLERANCE			
UNLESS OTHERWISE STATED			
X.X	±0.25	∠	±2°
X.XX	±0.15	UNIT	mm
REV	A/04	SCALE	1:1
SIZE	A4	SHEET	1 OF 1

7	COVER	ABS
6	LED	GaAsP/GaP
5	TERMINAL	H65(C2680)
4	CONTACT	SUS
3	BUTTON	PA66
2	FIXITY	PA66
1	HOUSING	PA66
ITEM	PARTNAME	MATERIAL



版本 VER	变更说明 CHANGE DESCRIPTION	日期 DATE	ECN NO.	版本 VERSION	A0	比例尺 SCALE	1:1	日期 DATE	2022.08.18	品名 TITLE	图号 DRAWING NO
				核准		核对		绘图	孙成	DS01-107RFL-U	XXXXXXX
版本 VER	变更说明 CHANGE DESCRIPTION	日期 DATE	ECN NO.	APPROVED BY		CHECKED BY		DRAWN BY	孙成	DS01-107RFL-U	XXXXXXX