

2SA1606/2SC4159

High-Voltage Switching, AF 100W Driver Applications

Applications

· High-voltage switching, AF power amplifier, 100W output predrivers.


Features

· Micaless package facilitating mounting.

Package Dimensions

unit:mm

2041A



(): 2SA1606

Specifications

Absolute Maximum Ratings at Ta = 25°C

- 1.000 1.1.1.1 1.1.1.1.1.1.1.1.1.1.1.1.1							
Parameter	Symbol	Conditions	Ratings	Unit			
Collector-to-Base Voltage	V _{CBO}		(–)180	V			
Collector-to-Emitter Voltage	VCEO		(–)160	V			
Emitter-to-Base Voltage	V _{EBO}		(–)6	V			
Collector Current	lс		(–)1.5	Α			
Collector Current (Pulse)	I _{CP}	Tc=25°C	(–)3	Α			
Collector Dissipation	PC		15	W			
Junction Temperature	Tj		150	°C			
Storage Temperature	Tstg		-55 to +150	°C			

Electrical Characteristics at Ta = 25°C

Parameter	Symbol	Conditions	Ratings			Unit
			min	typ	max	Unit
Collector Cutoff Current	ICBO	V _{CB} =(-)120V, I _E =0			(–)10	μA
Emitter Cutoff Current	IEBO	V _{EB} =(-)4V, I _C =0			(–)10	μA
DC Current Gain	hFE	V _{CE} =(-)5V, I _C =(-)300mA	60*		200*	
Gain-Bandwidth Product	f _T	V _{CE} =(-)10V, I _C =(-)50mA		100		MHz
Output Capacitance	C _{ob}	V _{CB} =(-)10V, f=1MHz		(30)23		pF
Base-to-Emitter Voltage	V _{BE}	$V_{CE}=(-)5V, I_{C}=(-)10mA$			(–)1.5	V

 $[\]ast$: The 2SA1606/2SC4159 are classified by 300mA h_{FE} as follows :

Continued on next page.


Rank	D	Е
hFE	60 to 120	100 to 200

- Any and all SANYO products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your SANYO representative nearest you before using any SANYO products described or contained herein in such applications.
- SANYO assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges,or other parameters) listed in products specifications of any and all SANYO products described or contained herein.

Continued from preceding page.

Parameter	Symbol	Conditions	Ratings			Unit
			min	typ	max	Uill
Collector-to-Emitter Saturation Voltage	V _{CE(sat)}	I _C =(-)500mA, I _B =(-)50mA		(-0.5)		V
				0.3		V
Collector-to-Base Breakdown Voltage	V(BR)CBO	I _C =(-)1mA, I _E =0	(–)180			V
Collector-to-Emitter Breakdown Voltage	V(BR)CEO	I _C =(−)1mA, R _{BE} =∞	(–)160			V
Emitter-to-Base Breakdown Votage	V _{(BR)EBO}	I _E =(-)1mA, I _C =0	(–)6			V
Turn-ON Time	ton	See specified test circuit.		(0.29)		μs
Turr-ON Time		See specified test circuit.		0.15		μs
Fall Time	t _f	See specified test circuit.		(0.19)		μs
		See specified test circuit.		0.48		μs
Storage Time	t _{stg}	See specified test circuit.		(0.48)		μs
		See specified test circuit.		0.81		μs


Switching Time Test Circuit





10l_{B1}= -10l_{B2}= l_C=0.5A

PW=20us


For PNP, the polarity is reversed.







2SA1606/2SC4159



2SA1606/2SC4159

- Specifications of any and all SANYO products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- SANYO Electric Co., Ltd. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all SANYO products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of SANYO Electric Co., Ltd.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the SANYO product that you intend to use.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. SANYO believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.

This catalog provides information as of November, 2003. Specifications and information herein are subject to change without notice.