

130MHz CDMA/AMPS Quadrature Modular and AGC

The HFA3767 is a monolithic bipolar quadrature modulator with gain control for CDMA/AMPS cellular applications. An upconverter quadrature mixer and an output gain control stage with better than 70dB of dynamic range are integrated in the design. A local oscillator input requires low drive levels and a divide by two phase shifter with duty cycle compensation achieves excellent phase and amplitude balance properties. The HFA3767 is one of the four chips in the PRISM™ chip set and is housed in a 20 lead SSOP package ideally suited to cellular handset applications.

Rochester Electronics Manufactured Components

Rochester branded components are manufactured using either die/wafers purchased from the original suppliers or Rochester wafers recreated from the original IP. All re-creations are done with the approval of the Original Component Manufacturer (OCM).

Parts are tested using original factory test programs or Rochester developed test solutions to guarantee product meets or exceeds the OCM data sheet.

Quality Overview

- ISO-9001
- AS9120 certification
- Qualified Manufacturers List (QML) MIL-PRF-35835
 - Class Q Military
 - Class V Space Level
- Qualified Suppliers List of Distributors (QSLD)
 - Rochester is a critical supplier to DLA and meets all industry and DLA standards.

Rochester Electronics, LLC is committed to supplying products that satisfy customer expectations for quality and are equal to those originally supplied by industry manufacturers.

The original manufacturer's datasheet accompanying this document reflects the performance and specifications of the Rochester manufactured version of this device. Rochester Electronics guarantees the performance of its semiconductor products to the original OCM specifications. 'Typical' values are for reference purposes only. Certain minimum or maximum ratings may be based on product characterization, design, simulation, or sample testing.



PRELIMINARY

February 1998

130MHz CDMA/AMPS Quadrature **Modulator and AGC**

Features

I/Q Amplitude and Phase Balance

| | The Amphicade and I have balance |
|---|---|
| • | 130MHz AGC Amplifier/Attenuator range>70dB |
| • | Low LO Drive Level10dBm |
| • | Power Enable/Disable Control |
| • | Single Supply Battery Operation 2.7 to 3.3V |

Applications

- IS95A CDMA/AMPS Dual Mode Handsets
- Wideband CDMA Handsets
- · Full Duplex Transceivers
- CDMA/TDMA Packet Protocol Radios
- · Portable Battery Powered Equipment



0.5dB 20

Description


The HFA3767 is a monolithic bipolar quadrature modulator with gain control CDMA/AMPS cellular applica-

tions. An upconverter quadrature mixer and an output gain control stage with better than 70dB of dynamic range are integrated in the design. A local oscillator input requires low drive levels and a divide by two phase shifter with duty cycle compensation achieves excellent phase and amplitude balance properties. The HFA3767 is one of the four chips in the PRISM™ chip set and is housed in a 20 lead SSOP package ideally suited to cellular handset applications...

Ordering Information


| PART NUMBER | TEMP. RANGE (^O C) | PACKAGE | PKG. NO. | | |
|-------------|----------------------------------|---------------|----------|--|--|
| HFA3767IA | -40 to 85 | 20 Ld SSOP | M20.15 | | |
| HFA3767IA96 | -40 to 85 | Tape and Reel | | | |

Pinout



HFA3767 (SSOP)

Simplified Block Diagram



PRISM™ and the PRISM™ logo are trademarks of Harris Corporation

Pin Descriptions

| Pin Number | NAME | DESCRIPTION |
|------------|----------|--|
| 1 | TX_PE | Power enable control input. HIGH for normal operation. LOW for power down. |
| 2 | GND | Bias and AGC control ground return. |
| 3 | TXI+ | Positive I channel baseband input. Requires a 1.2VDC common mode bias voltage. |
| 4 | TXI- | Negative I channel baseband input. Requires a 1.2VDC common mode bias voltage. |
| 5 | NC | No connect pin. Tie to ground to improve isolation from I to Q channels. |
| 6 | TXQ- | Negative QI channel baseband input. Requires a 1.2VDC common mode bias voltage. |
| 7 | TXQ+ | Positive Q channel baseband input. Requires a 1.2VDC common mode bias voltage. |
| 8 | MIX_GND | Quadrature Mixers ground return. |
| 9 | DPS_GND | Digital Phase shifter ground return. |
| 10 | DPS_VCC | Digital Phase Shifter Power Supply. Use high quality RF decoupling capacitors right at the pin. |
| 11 | LO_GND | Local Oscillator Input ground return. |
| 12 | LO_IN | Local Oscillator Current Input. Use a 50Ω power to current converter. See applications diagram. |
| 13 | CAP | AGC Bias circuit filter capacitor. Typical value of 1000pF to 10000pF. |
| 14 | AGC_GND | AGC circuit ground return. |
| 15 | TX_IF+ | Positive IF output port. Requires a DC return to VCC thru a choke or match inductor. |
| 16 | TX_IF- | Negative IF output port. Requires a DC return to VCC thru a choke or match inductor. |
| 17 | AGC_VCC | AGC circuit Power Supply.Use high quality RF decoupling capacitors right at the pin. |
| 18 | GCT | Gain and temperature compensation external resistor. See applications diagram. |
| 19 | AGC_CTRL | AGC control input. Require a 1% resistor divider at this input. See applications diagram. |
| 20 | VCC | Bias and AGC control Power Supply.Use high quality RF decoupling capacitors right at the pin. |

Absolute Maximum RatingsTA = 25°CThermal InformationSupply Voltage-0.3V to +3.6VThermal Resistance (Typical, Note 1)Voltage on Any Other Pin-0.3V to VCC +0.3VSSOP Package

θ_{JA} (°C/W)

Operating Conditions

CAUTION: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress only rating and operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied.

(Lead Tips Only)

NOTE:

1. θ_{JA} is measured with the component mounted on an evaluation PC board in free air.

Electrical Specifications VCC = 2.7V to 3.3V, LO_IN = -10dBM @ 260MHz. Refer to Applications diagram

| PARAMETER | TEST CONDITIONS | (Note 2) TEST LEVEL | TEMP (°C) | MIN | TYP | MAX | UNITS | |
|--|---|---------------------------|--------------|------------|------------|--------------|--------|--|
| CDMA MODE SPECIFICATIONS: I AND Q INPUTS @ 0.63Vpp Sinusoidal, 500KHz in Quadrature (SSB Output) | | | | | | | | |
| Output Power into 50Ω | Vagc = 0.5V , Output | Α | 25 | -13.1 | -12.7 | -12.3 | dBm | |
| P1dBO/Output Power Ratio | from 400 to 50Ω Dif- ferential to single end | Α | Full | 8 | 12.4 | - | dB | |
| Output Noise Floor | converter (0dB Attenuation) | В | 25 | - | -142.3 | -140 | dBm/Hz | |
| P1dBO/Output Power Ratio | AGC_CTRL set for | В | Full | 8 | 12.4 | - | dB | |
| Output Noise Floor | 10dB of attenuation | В | 25 | - | -144 | - | dBm/Hz | |
| P1dBO/Output Power Ratio | AGC_CTRL set for | В | 25 | 8 | 12.4 | - | dB | |
| Output Noise Floor | 20dB of attenuation | В | 25 | - | -148.5 | - | dBm/Hz | |
| P1dBO/Output Power Ratio | AGC_CTRL set for | В | 25 | 8 | 12.4 | - | dB | |
| Output Noise Floor | 30dB of attenuation | В | 25 | - | -153.4 | - | dBm/Hz | |
| P1dBO/Output Power Ratio | AGC_CTRL set for | Α | Full | 8 | 12.4 | - | dB | |
| Output Noise Floor | 40dB of attenuation | В | 25 | - | -160 | - | dBm/Hz | |
| P1dBO/Output Power Ratio | AGC_CTRL set for | Α | Full | 8 | 12.4 | - | dB | |
| Output Noise Floor | 50dB of attenuation | В | 25 | - | -163 | - | dBm/Hz | |
| P1dBO/Output Power Ratio | AGC_CTRL set for | В | 25 | 8 | 12.4 | - | dB | |
| Output Noise Floor | 70dB of attenuation | В | 25 | - | -165 | -162 | dBm/Hz | |
| FM MODE SPECIFICATIONS Q INF | UT ONLY @ 0.44Vpp DC diff | erential at | Q input. C | ommom m | ode voltag | e at l input | | |
| Output Power into 50Ω | Vagc = 0.5V , Output | Α | Full | -10.2 | -9.76 | -9.3 | dBm | |
| P1dBO/Output Power Ratio | from 400 to 50Ω Dif- ferential to single end | Α | Full | 7 | 10.2 | - | dB | |
| Output Noise Floor | converter (0dB Attenuation) | В | 25 | - | -142.3 | -140 | dBm/Hz | |
| GENERAL SPECIFICATIONS: I AN | D Q INPUTS @ 0.63Vpp Sinu | soidal, 500 | KHz in Qu | adrature (| SSB Outpu | t) | | |
| AGC Gain Control Voltage | | Α | 25 | 0.5 | - | 2.4 | ٧ | |
| AGC Gain Control Sensitivity | | В | 25 | - | 50 | - | dB/V | |

Electrical Specifications VCC = 2.7V to 3.3V, LO_IN = -10dBM @ 260MHz. Refer to Applications diagram

| | | (Note 2) | | | | | |
|---------------------------------------|--|---------------|--------------|-------------|-----------|------|---------|
| PARAMETER | TEST CONDITIONS | TEST LEVEL | TEMP (°C) | MIN | ТҮР | MAX | UNITS |
| AGC Gain Control Input Impedance | Externally set | С | 25 | - | 18 | - | ΚΩ |
| AGC Switching Speed, Full Scale | To ±1dB Settling | В | 25 | - | - | 10 | μs |
| AGC Insertion Phase | 20dB step | В | 25 | - | 1.6 | - | deg/dB |
| IF Frequency Range | Applications diagram | В | 25 | - | 130 | - | MHz |
| GENERAL SPECIFICATIONS: I AND Q IN | NPUTS @ 0.63Vpp Sinu | ısoidal, 500 | KHz in Qu | adrature (S | SSB Outpu | t) | |
| TX_IF single end equivalent series R | 130MHZ, IF+ or IF- | В | 25 | - | 115 | - | Ω |
| TX_IF single end equivalent series C | 130MHz, IF+ or IF- | В | 25 | - | 4.9 | - | pF |
| Baseband Frequency Range | | В | 25 | DC | | 1.0 | MHz |
| LO Frequency Range | Applications diagram | Α | 25 | - | 260 | - | MHz |
| Amplitude Balance (Note 3) | Deviation from ideal | В | 25 | -0.5 | - | +0.5 | dB |
| Phase Balance (Note 3) | SSB characteristics AGC_CTRL = 0.5V | В | 25 | -2 | - | +2 | Degrees |
| Single Sideband Suppression | | Α | Full | 32 | 35 | | dBc |
| Carrier Suppression | (Vagc= 0.5V) (0dB attenuation) | Α | 25 | -30 | - | - | dBc |
| | AGC_CTRL set for 20dB attenuation | А | 25 | -30 | - | - | dBc |
| | AGC_CTRL set for 70dB attenuation | В | 25 | -29 | | - | dBc |
| LO Input Impedance | Single end | С | 25 | - | 130 | - | Ω |
| LO Drive Level | Applications diagram | Α | 25 | | -10 | | dBm |
| LO Drive Optimal Current Range | | В | 25 | 50 | 200 | 300 | μArms |
| Baseband Differential Input Impedance | | С | 25 | 2K | - | - | Ω |
| VCM Common mode Input Voltage | Into I+,I-,Q+and Q- | Α | Full | 1.14 | 1.20 | 1.26 | ٧ |
| POWER SUPPLY AND LOGIC SPECIFIC | ATIONS | | | | • | | |
| Supply Voltage Range | | В | 25 | 2.7 | - | 3.3 | ٧ |
| Supply Current @ 3.3V | AGC_CTRL = 0.5V | Α | Full | - | - | 40 | mA |
| | AGC_CTRL = 2.4V | Α | Full | - | - | 25 | mA |
| Power Down Supply Current | TX_PE = Low | Α | 25 | - | - | 100 | μΑ |
| Power Down Speed | | В | Full | - | - | 10 | μs |
| TX_PE V _{IL} | | Α | Full | - | - | 0.8 | ٧ |
| TX_PE V _{IH} | | Α | Full | 2.0 | - | - | ٧ |
| TX_PE Input Bias Current @ VCC = 3.3V | PE = 2.0V | Α | Full | -50 | - | +50 | μΑ |
| | PE = 0.66V, 2.7VCC | Α | Full | -50 | - | +50 | μΑ |

^{2.} A = Production Tested, B = Based on Characterization, C = By Design
3. I leading Q produces a positive frequency offset from the carrier (USB). Test garanteed by sideband suppression.

Applications Diagram vcc **POWER ENABLE** -O AGC_CTRL TX_PE vcc AGC CTRL Bias 3.6k 1% GND Control I+ Q-I- O-**O** IF+ Q- **Q-**O IF-4.7p Q+ **0**-AGC_GND Murata LFSH33 CAP MIX GND 0°/90° DPS_GND LO_IN LO_GND DPS_VCC LO_IN TEST OUTPUT NETWORK Differential to 50Ω Single end Converter (1.1dB insertion loss) 50Ω output Mini Circuits. TC8-1 TX_IF+