

### ■ PRODUCT CHARACTERISTICS



$V_{DSS}$	60V
$R_{DS(on)}(typ)(@V_{GS}=10\text{ V})$	56mΩ
$R_{DS(on)}(typ)(@V_{GS}=4.5\text{ V})$	63mΩ
$I_D$	7A

### ■ APPLICATIONS

- Portable Equipment and Battery Powered systems.
- Power Management in Notebook Computer

### ■ FEATURES

- Lower  $R_{DS(ON)}$  to Minimize Conduction Losses
- Reliable and Rugged
- ROHS Compliant & Halogen-Free
- 100% UIS and Rg Tested



PDFNX3-8L

### ■ ORDER INFORMATION

Order codes		Package	Packing
Halogen-Free	Halogen		
N/A	MOT6568J	PDFN3X3-8L	5000 pieces/Reel

### ■ ABSOLUTE MAXIMUM RATINGS ( $T_J=25^\circ\text{C}$ Unless Otherwise Noted)

PARAMETER	SYMBOL	RATINGS	UNIT
Drain-Source Voltage	$V_{DSS}$	60	V
Gate-Source Voltage	$V_{GSS}$	$\pm 20$	V
Drain Current Continuous	$I_D$	7	A
Drain Current Continuous( $T_c=100^\circ\text{C}$ )	$I_D(100^\circ\text{C})$	5	A
Drain Current Pulsed	$I_{DM}$	40	A
Power Dissipation	$P_D$	2.1	W
Junction to Ambient	$R_{\theta JA}$	60	$^\circ\text{C}/\text{W}$
Junction Temperature	$T_J$	+150	$^\circ\text{C}$
Storage Temperature Range	$T_{STG}$	-55 ~ +150	$^\circ\text{C}$

**■ ELECTRICAL CHARACTERISTICS (T<sub>C</sub>=25°C unless otherwise specified)**

PARAMETER	SYMBOL	CONDITION	MIN	TYP	MAX	UNIT
<b>Off characteristics</b>						
Drain-Source Breakdown Voltage	BV <sub>DSS</sub>	V <sub>GS</sub> =0V, I <sub>D</sub> =250μA	60	69	-	V
Zero Gate Voltage Drain Current	I <sub>DSS</sub>	V <sub>DS</sub> =60V, V <sub>GS</sub> =0V	-	-	1	μA
Gate-Body Leakage Current	I <sub>GSS</sub>	V <sub>GS</sub> =±20V, V <sub>DS</sub> =0V	-	-	±100	nA
<b>On characteristics</b>						
Gate Threshold Voltage	V <sub>GS(th)</sub>	V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =250μA	1.0	1.4	2.0	V
Drain-Source On-State Resistance	R <sub>D(S)ON</sub>	V <sub>GS</sub> =10V, I <sub>D</sub> =5A	-	56	60	mΩ
		V <sub>GS</sub> =4.5V, I <sub>D</sub> =4A	-	63	70	mΩ
Forward Transconductance	g <sub>FS</sub>	V <sub>DS</sub> =5V, I <sub>D</sub> =7A	5	-	-	S
<b>Dynamic characteristics</b>						
Input Capacitance	C <sub>iss</sub>	V <sub>DS</sub> =25V, V <sub>GS</sub> =0V, F=1.0MHz	-	1920	-	PF
Output Capacitance	C <sub>oss</sub>		-	155	-	PF
Reverse Transfer Capacitance	C <sub>rss</sub>		-	116	-	PF
<b>Switching characteristics</b>						
Turn-on Delay Time	t <sub>d(on)</sub>	V <sub>DS</sub> =30V, R <sub>L</sub> =4.7Ω V <sub>GS</sub> =10V, R <sub>GEN</sub> =3Ω	-	8	-	nS
Turn-on Rise Time	t <sub>r</sub>		-	5	-	nS
Turn-Off Delay Time	t <sub>d(off)</sub>		-	29	-	nS
Turn-Off Fall Time	t <sub>f</sub>		-	6	-	nS
Total Gate Charge	Q <sub>g</sub>	V <sub>DS</sub> =30V, I <sub>D</sub> =7A, V <sub>GS</sub> =10V	-	50	-	nC
Gate-Source Charge	Q <sub>gs</sub>		-	8	-	nC
Gate-Drain Charge	Q <sub>gd</sub>		-	16	-	nC
<b>Drain-source diode characteristics</b>						
Diode Forward Voltage	V <sub>SD</sub>	V <sub>GS</sub> =0V, I <sub>S</sub> =7A	-	-	1.2	V
Diode Forward Current	I <sub>S</sub>		-	-	7	A
Reverse Recovery Time	t <sub>rr</sub>	T <sub>J</sub> = 25°C, I <sub>F</sub> = 7A di/dt = 100A/μs	-	35	-	nS
Reverse Recovery Charge	Q <sub>rr</sub>		-	43	-	nC
Forward Turn-On Time	t <sub>on</sub>	Intrinsic turn-on time is negligible (turn-on is dominated by LS+LD)				

## ■ TYPICAL CHARACTERISTICS




Figure 1 Output characteristics



Figure 2  $R_{DS(on)}$ -junction temperature

Figure 3 Transfer characteristics




Figure 4 Gate charge



Figure 5  $R_{DS(on)}$ -drain current

Figure 6 Source-drain diode forward

## ■ TYPICAL CHARACTERISTICS(Cont.)




Figure 7 Capacitance vs vds




Figure 8 Power de-rating




Figure 9 Safe operation area




Figure 10 Current de-rating






Figure 11 Normalized maximum transient thermal impedance

## ■ PDFN3X3-8L Package Mechanical Data



SYMBOL	DIMENSIONAL REQS		
	MIN	NOM	MAX
A	0.70	0.75	0.80
b	0.25	0.30	0.35
c	0.10	0.15	0.25
D	3.25	3.35	3.45
D1	3.00	3.10	3.20
D2	1.78	1.88	1.98
D3	---	0.13	---
E	3.20	3.30	3.40
E1	3.00	3.15	3.20
E2	2.39	2.49	2.59
e	0.65BSC		
H	0.30	0.39	0.50
L	0.30	0.40	0.50
L1	---	0.13	---
$\theta$	---	10°	12°
M	*	*	0.15

\* Not specified