






N ATTENUATOR 3 DB 3 GHZ 50W

PAGE 1/2 ISSUE 10-03-16B SERIES PART NUMBER R417003110

SCALE 1:2







All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)
5 1	074111 F00 07FF1	DAGGNATED
Body	STAINLESS STEEL	PASSIVATED
Male center contact	BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL PHOSPHORUS 2
Female center contact	BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL PHOSPHORUS 2
Outer contact	-	-
Insulator	PTFE	
Gasket	SILICONE RUBBER	
Substrate	ALUMINA	
Resistor	THICK FILM	
Others parts	ALUMINIUM	BLACK PAINTING





N ATTENUATOR 3 DB 3 GHZ 50W

PAGE 2/2	ISSUE 10-03-16B	SERIES ATTENUATOR	PART NUMBER R417003110
-----------------	-----------------	----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 1	1 - 2	2 - 3
V.S.W.R (≤)	1.10	1.25	1.35
Deviation(±dB)	0.70	0.70	0.70

Operating Frequency Range	DC - 3	GHz
Impedance	50	Ω
Nominal Attenuation	3	dB
Peak power at 25°C (1µs, 1‰)	5000	W
Average power at 25°C	50	W (Free Air Cooled)
		W (Conduction Cooled)


MECHANICAL CHARACTERISTICS

Connectors	N	Male Female	MIL-C 39012
Weight	431,8200 g		

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55 /+125 °C
Storage temperature range	-55 /+125 °C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS