

Summary

[Request a quote](#)

[Catalog](#)

Coax	1
Locking system	Push-pull
Series	00 - NIM-CAMAC

Technical details

Electrical Configuration

Coax	1
Insert configuration value	0.25 - 1 Coax (50 Ohm)
Insulator	T: PTFE
Rated current	4 Amps
Contact Type	Coaxial 50 Ohm
Test voltage	1.1 kV (rms)

Form & Material

Shell style / Model id	FTA - T-plug with two in line receptacles
Housing material	Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces
Locking system	Push-pull
Keying	Circular (can rotate)
Weight	7.2 g

https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/fta-00-250-ctf.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.


Environment

Environmental protection	IP50
F ret (min)	100 N
Salt Spray Corrosion	>1000 hr

Cable fixation

Cable termination protection	Standard back nut (no additional protection)
Fixation type	Cable collet

Drawings



Dimensions

	L	I	H	A
mm.	30	9.5	17.5	9
in.	1.18	0.37	0.69	0.35

https://www.lemo.com/int_en/solutions/specialties/00-nim-camac/fta-00-250-ctf.html

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.