



RFCPL0605 Series – RoHS Compliance

MULTILAYER CERAMIC COUPLER

Halogens Free Product

2.4 GHz / 5 GHz Dual Band RF Application

P/N: RFCPL0605030LPT

*Contents in this sheet are subject to change without prior notice

Approval sheet



FEATURES


- 1. Miniature footprint: 0.65 X 0.50 X 0.35 mm³
- 2. Low Insertion Loss
- 3. High Rejection Rate
- 4. LTCC Process

APPLICATIONS

1. 2.4GHz / 5GHz band RF Application

CONSTRUCTION

Top view




PIN	Connection	ction PIN Connec	
P1	Coupling	P3	Output
P2	Terminate	P4	Input

DIMENSIONS

Figure	Symbol	Dimension (mm)
	L	0.65 ± 0.10
	W	0.50 ± 0.10
Top view Side view	Т	0.35 ± 0.05
Side view	A	0.225±0.10
	В	0.20 ± 0.05
Bottom view	С	0.125 ± 0.05
	D	0.25 ± 0.05




ELECTRICAL CHARACTERISTICS



LAND PATTERN

Figure





Approval sheet

RFI	IARII	ITY	TEST

Test item	Test condition / Test method	Specification		
Solderability	*Solder bath temperature : $235 \pm 5^{\circ}C$	At least 95% of a surface of each terminal		
JIS C 0050-4.6	*Immersion time:2 \pm 0.5 sec	electrode must be covered by fresh solder.		
JESD22-B102D	Solder : Sn3Ag0.5Cu for lead-free			
Resistance to soldering heat	*Preheating temperature : $120~150^{\circ}C$,	No mechanical damage.		
JIS C 0050-5.4	1 minute.	Electrical specification shall satisfy the		
	*Solder temperature : 270±5°C	descriptions in electrical characteristics under		
	*Immersion time:10±1 sec	the operational temperature range within -40		
	Solder : Sn3Ag0.5Cu for lead-free	~ 85°C.		
	Measurement to be made after keeping at	Loss of metallization on the edges of each		
	room temperature for 24±2 hrs	electrode shall not exceed 25%.		
Drop Test	*Height : 75 cm	No mechanical damage.		
JIS C 0044	*Test Surface : Rigid surface of concrete or	Electrical specification shall satisfy the		
Customer's specification.	steel.	descriptions in electrical characteristics under		
	*Times : 6 surfaces for each units ; 2 times	the operational temperature range within -40		
	for each side.	~ 85°C.		
Vibration	*Frequency:10Hz~55Hz~10Hz(1min)	No mechanical damage.		
JIS C 0040	*Total amplitude : 1.5mm	Electrical specification shall satisfy the		
	*Test times : 6hrs.(Two hrs each in three	descriptions in electrical characteristics under		
	mutually perpendicular directions)	the operational temperature range within -40 ~ 85°C.		
Adhesive Strength	*Pressurizing force :	No remarkable damage or removal of the		
of Termination	2N(≦0603 ; 1.6 x 0.8 mm) ;	termination.		
JIS C 0051- 7.4.3	10N(>0603 ; 1.6 x 0.8 mm)			
	*Test time:5±1 sec			
Bending test	The middle part of substrate shall be	No mechanical damage.		
JIS C 0051- 7.4.1	pressurized by means of the pressurizing rod	Electrical specification shall satisfy the		
	at a rate of about 1 mm/s per second until the	descriptions in electrical characteristics under		
	deflection becomes 1mm/s and then pressure	the operational temperature range within -40		
	shall be maintained for 5 ± 1 sec.	~ 85°C.		
	Measurement to be made after keeping at			
	room temperature for 24±2 hours			



Approval sheet

Temperature cycle	1. 30±3 minutes at -40°C±3°C,	No mechanical damage.		
JIS C 0025	2. 10~15 minutes at room temperature,	Electrical specification shall satisfy the		
	3. 30±3 minutes at +85°C±3°C,	descriptions in electrical characteristics		
	4. 10~15 minutes at room temperature,	under the operational temperature range		
	Total 100 continuous cycles	within -40 ~ 85°C.		
	Measurement to be made after keeping at			
	room temperature for 24±2 hrs			
High temperature	*Temperature: 85°C±2°C	No mechanical damage.		
JIS C 0021	*Test duration : 1000+24/-0 hours	Electrical specification shall satisfy the		
	Measurement to be made after keeping at	descriptions in electrical characteristics under		
	room temperature for 24±2 hrs	the operational temperature range within -40		
		~ 85°C.		
Humidity	*Humidity : 90% to 95% R.H.	No mechanical damage.		
(steady conditions)	*Temperature : 40±2°C	Electrical specification shall satisfy the		
JIS C 0022	*Time : 1000+24/-0 hrs.	descriptions in electrical characteristics under		
	Measurement to be made after keeping at room temperature for 24 ± 2 hrs	the operational temperature range within -40 ~ 85°C.		
	% 500hrs measuring the first data then			
	1000hrs data			
Low temperature	*Temperature : -40°C±2°C	No mechanical damage.		
JIS C 0020	*Test duration : 1000+24/-0 hours	Electrical specification shall satisfy the		
	Measurement to be made after keeping at	descriptions in electrical characteristics under		
	room temperature for 24±2 hrs	the operational temperature range within -40 ~ 85°C.		
		~ 00 0.		



SOLDERING CONDITION

Typical examples of soldering processes that provide reliable joints without any damage are given in Fig 2,





Fig 2. Infrared soldering profile

ORDERING CODE

RF	CPL	060503	0	L	Р	Т
Walsin	Product	Dimension code	Unit of	Application	Code from	T: Taping
RF device	Code:	Per 2 digits of Length,	dimension	L: 2400~2500 MHz	Design Code	
	Coupler	Width, Thickness :	0 : 0.1 mm	/ 4900~5850 MHz		
		e.g. :	1 : 1.0 mm			
		060503 =				
		Length 06,				
		Width 05, Thickness 03				

Minimum Ordering Quantity: 4000 pcs per reel. PACKAGING




Paper Tape specifications (unit :mm)

Index	Ao	Во	ΦD	Т	W
Dimension (mm)	0.62 ± 0.10	$\textbf{0.80} \pm \textbf{0.10}$	1.55 ± 0.05	$\textbf{0.43}\pm\textbf{0.10}$	8.00 ± 0.10
Index	E	F	Po	P1	P2
Dimension (mm)	1.75 ± 0.10	$\textbf{3.50} \pm \textbf{0.05}$	4.00 ± 0.10	2.00 ± 0.05	2.00 ± 0.05



Reel dimensions



Taping Quantity: 4000 pieces per 7" reel

CAUTION OF HANDLING

Limitation of Applications

Please contact us before using our products for the applications listed below which require especially high reliability for the prevention of defects, which might directly cause damage to the third party's life, body or property.

- (1) Aircraft equipment
- (2) Aerospace equipment
- (3) Undersea equipment
- (4) Medical equipment
- (5) Disaster prevention / crime prevention equipment
- (6) Traffic signal equipment
- (7) Transportation equipment (vehicles, trains, ships, etc.)
- (8) Applications of similar complexity and /or reliability requirements to the applications listed in the above.

Storage condition

- (1) Products should be used in 6 months from the day of WALSIN outgoing inspection.
- (2) Storage environment condition.
 - Products should be storage in the warehouse on the following conditions.
 - Temperature : +5 to +40°C
 - Humidity : 30 to 70% relative humidity
 - Don't keep products in corrosive gases such as sulfur. Chlorine gas or acid or it may cause oxidization of electrode, resulting in poor solderability.
 - Products should be storage on the palette for the prevention of the influence from humidity, dust and son on.
 - Products should be storage in the warehouse without heat shock, vibration, direct sunlight and so on.
 - Products should be storage under the airtight packaged condition.