



Spec No.: DS30-2006-042 Effective Date: 06/24/2010 Revision: C



BNS-OD-FC001/A4

LITE-ON Technology Corp. / Optoelectronics No.90,Chien 1 Road, Chung Ho, New Taipei City 23585, Taiwan, R.O.C. Tel: 886-2-2222-6181 Fax: 886-2-2221-1948 / 886-2-2221-0660 http://www.liteon.com/opto

**Property of Lite-on Only** 

#### **FEATURES**

\* 0.4 inch (10 mm ) DIGIT HEIGHT.
\* CONTINUOUS UNIFORM SEGMENTS.
\* LOW POWER REQUIREMENT.
\* EXCELLENT CHARACTERS APPEARANCE.
\* HIGH BRIGHTNESS & HIGH CONTRAST.
\* WIDE VIEWING ANGLE.
\* SOLID STATE RELIABILITY.
\* CATEGORIZED FOR LUMINOUS INTENSITY.
\* LEAD-FREE PACKAGE (ACCORDING TO ROHS)

#### DESCRIPTION


The LTS-4801KF is a 0.4 inch (10 mm) height single digit seven-segment display. This device utilizes AlInGaP yellow orange LED chips, which are made from AlInGaP on a non-transparent GaAs substrate, and has a gray face and white segments.

### DEVICE

PART NO.	DESCRIPTION		
AlInGaP Yellow Orange	Common Anode		
LTS-4801KF	Rt. Hand Decimal		

PART NO.:LTS-4801KF
---------------------


Property of Lite-on Only



PART NO.:LTS-4801KF

Property of Lite-on Only

#### INTERNAL CIRCUIT DIAGRAM



### **PIN CONNECTION**

No	CONNECTION
1	CATHODE G
2	CATHODE F
3	COMMON ANODE
4	CATHODE E
5	CATHODE D
6	CATHODE D.P.
7	CATHODE C
8	COMMON ANODE
9	CATHODE B
10	CATHODE A

PART NO.:LTS-4801KF

**Property of Lite-on Only** 

## ABSOLUTE MAXIMUM RATING AT Ta=25°C

PARAMETER	MAXIMUM RATING	UNIT			
Power Dissipation Per Segment	70	mW			
Peak Forward Current Per Segment	60	mA			
(1/10 Duty Cycle, 0.1ms Pulse Width )					
Continuous Forward Current Per Segment	25	mA			
Derating Linear From 25°C Per Segment	0.28	mA/ºC			
Reverse Voltage Per Segment	5	V			
Operating Temperature Range	-35°C to +105°C				
Storage Temperature Range	-35°C to +105°C				
Solder Conditions: 1/16 inch below seating plane for 3 seconds at 260°C.,					
or temperature of unit (during assembly) not over max. temperature rating above					

### ELECTRICAL / OPTICAL CHARACTERISTICS AT Ta=25°C

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	IV	27520	44000		μcd	IF=20mA
Peak Emission Wavelength	λp		611		nm	IF=20mA
Spectral Line Half-Width	Δλ		17		nm	IF=20mA
Dominant Wavelength	λd		605		nm	IF=20mA
Forward Voltage Per Segment	VF		2.05	2.6	V	IF=20mA
Reverse Current Per Segment	IR			100	μΑ	VR=5V
Luminous Intensity Matching Ratio (Similar Light Area)	IV-m			2:1		IF=20mA

Note: Luminous intensity is measured with a light sensor and filter combination that approximates the CIE (Commision Internationale De L'Eclairage) eye-response curve.

**Property of Lite-on Only** 

#### **TYPICAL ELECTRICAL / OPTICAL CHARACTERISTIC CURVES**

