

512 Bit Electrically Alterable Read Only Memory

FEATURES

- 64 word x 8 bit organization
- 6 bit binary addressing
- +5, -28V power supplies
- Word Alterable
- 10 year data storage for ER2055 (at +70°C)
- 1 year data storage for ER2055 IR (at +85°C) and ER2055 HR (at +125°C)
- TTL compatible with pull-up resistors on inputs
- Tri-state outputs
- Read Time: 2μs (ER2055), 4μs (ER2055 IR and ER2055 HR)
- Write/Erase Time: 50ms (ER2055), 100ms (ER2055 HR)
- No voltage switching required
- 2 chip selects
- 2 chip selects
- Two extended temperature ranges:
-40°C to +85°C (Industrial) Part # ER2055 IR
-55°C to +125°C (Hi-Rel) Part # ER2055 HR

DESCRIPTION

The ER2055 is a fully decoded 64 x 8 electrically erasable and reprogrammable ROM. Write, erase, and read voltages are switched internally via a 2-bit code applied to C1 and C2.

Data is stored by applying negative writing pulses that selectively tunnel charge into the oxide-nitride interface of the gate insulator of the 512 MNOS memory transistors. When the writing voltage is removed the charge trapped at the interface is manifested as a negative shift in the threshold voltage of the selected memory transistors.

OPERATION

Data is stored in a two transistor memory cell. After the cell is preconditioned by an erase signal (which causes a positive shift in the threshold of both transistors), data is written into one of the transistors making its threshold more negative. A sensing flip flop is used to read the memory cell and presents a logic high or low to the output depending on which transistor is "written".

The ER2055 EAROM may be operated with V_{SS} between +5 and +10 volts for either TTL or CMOS compatibility. The negative power supply, V_{GG} , should be adjusted so that the difference between V_{SS} and V_{GG} is always 33 volts.


It is important to note two things: first, that an erase is required before a write to precondition the cell, and second, that after an erase, both transistors will have the same threshold voltage and valid data will not be present at the output.

PIN FUNCTIONS


A_0 - A_5	6-Bit Word Address	
D_0 - D_7	Data input and output pins	
CS_1 , $\overline{CS_2}$	Chip Selects Chip selected at logic "1" on CS_1 and logic "0" on $\overline{CS_2}$. When chip is not selected, outputs are open circuit, read, write and erase are disabled. Power is reduced.	
C_1 , C_2	Mode Control Inputs	
$\overline{C_1}$	$\overline{C_2}$	
0	1	Erase Mode: stored data is erased at addressed location.
1	Don't Care	Read Mode: addressed data read after clock pulse. Output data retained at output pins until chip deselected or control lines switched.
0	0	Write Mode: input data written at addressed location. Clock not required.
CLK	Clock Input. Pulse to logic "1" for read operation.	
V_{SS}	Substrate supply. Normally at +5 volts.	
V_{G1}	Ground Input.	
V_{GG}	Power Supply Input. Normally at -28 volts.	

PIN CONFIGURATION

22 LEAD DUAL IN LINE



BLOCK DIAGRAM



The ER2055 EAROM uses dynamic edge triggered circuits internally. This requires either a mode change, a clock or a transition of the chip selects between successive operations. Thus successive operations in the same mode must be separated by transition of one of these four lines. Clock pulses are not normally required during erase or write operations, but are needed for successive operations if the chip is continuously selected, i.e., applications where one EAROM is used.

The ER2055IR and ER2055HR are screened to Mil Std. 883B/method 5004, 1/level B, pre-cap visual inspection, environmental testing, burn-in and external visual. They are available in 28 lead ceramic dual in-line packages.

ELECTRICAL CHARACTERISTICS**Maximum Ratings***

All inputs and outputs (with respect to V_{SS}) $-35V$ to $+0.3V$
 Storage temperature $-65^{\circ}C$ to $+150^{\circ}C$
 Soldering temperature of leads (10 seconds) $+300^{\circ}C$

Standard Conditions (for TTL Compatibility)

$V_{SS} = +5V \pm 5\%$

$V_{GG} = -28V \pm 5\%$

$V_{GI} = GND$

Operating Temperature $T_A = 0^{\circ}C$ to $+70^{\circ}C$ for ER2055 $T_A = -40^{\circ}C$ to $+85^{\circ}C$ for ER2055IR $T_A = -55^{\circ}C$ to $+125^{\circ}C$ for ER2055HR


Output Load = 100pF, 1 TTL load

* Exceeding these ratings could cause permanent damage to the device. This is a stress rating only and functional operation of this device at these conditions is not implied—operating ranges are specified in Standard Conditions. Exposure to absolute maximum rating conditions for extended periods may affect device reliability. Data labeled "typical" is presented for design guidance only and is not guaranteed.


Characteristics	Sym	ER2055			ER2055 IR/ER2055 HR			Units	Conditions
		Min.	Typ.**	Max.	Min.	Typ.**	Max.		
DC CHARACTERISTICS									
Input Logic "1"	V_{IH}	$V_{SS} - 1.5$	—	$V_{SS} + 0.3$	$V_{SS} - 1.5$	—	$V_{SS} + 0.3$	V	
Input Logic "0"	V_{IL}	$V_{SS} - 15$	—	0.8	$V_{SS} - 10$	—	0.6	V	
Output Logic "1"	V_{OH}	$V_{SS} - 1.5$	—	—	$V_{SS} - 1.5$	—	—	V	$I_{OH} = 100\mu A$
Output Logic "0"	V_{OL}	—	—	0.6	—	—	0.6	V	$I_{OL} = 1.6mA$ for $V_{SS} = 5V$
Input Leakage	I_L	—	2	10	—	2	10	μA	$V_{IN} = V_{SS} - 15$
Output Leakage	I_O	—	2	10	—	2	10	μA	Chip deselected
Power Supply Current									
Read	I_{GG}	—	8	10	—	8	18	mA	I_{SS} approx. I_{GG}
Write	I_{GG}	—	6	7	—	6	9	mA	I_{SS} approx. I_{GG}
Erase	I_{GG}	—	4	7	—	6	8	mA	I_{SS} approx. I_{GG}
Deselected	I_{GG}	—	4	7	—	4	6	mA	I_{SS} approx. I_{GG}
AC CHARACTERISTICS									
Access Time	t_{ACC}	—	—	2.0	—	—	4.0	μs	
Clock Pulse width	t_{PW}	2.0	—	20.0	2.0	—	20.0	μs	
Erase Cycle Time	t_E	50	—	200.0	100	—	200.0	ms	
Write Cycle Time	t_W	50	—	200.0	100	—	200.0	ms	
Read Cycle Time	t_R	5.0	—	24.0	6.0	—	25.0	μs	
Address to Clock Time	t_A	50	—	—	50	—	—	ns	
Data Set Up Time	t_{DS}	50	—	—	50	—	—	ns	
Data Hold Time	t_{DH}	50	—	—	50	—	—	ns	
Control to Address & Data Change	t_C	0	—	—	0	—	—	ns	
Number of Reads/Word Refresh	N_{RA}	10^{11}	—	—	10^{11}	—	—	—	
Number of Erase/Write Cycles	N_W	10^6	—	—	10^6	—	—	—	
Input Capacitance, all pins	C_{IO}	—	6	10	—	6	10	pF	
Unpowered Data Storage Time	t_S	10	—	—	1	—	—	Years	at max. temperature
Power Dissipation Read Cycle	P_D	—	450	500	—	450	500	mW	at $25^{\circ}C$ $V_{SS} = +5$, $V_{GG} = -29$
	P_D	—	not applicable		—	—	500	mW	at $125^{\circ}C$ $V_{SS} = +5$, $V_{GG} = -29$
	P_D	—	not applicable		—	—	600	mW	at $-55^{\circ}C$ $V_{SS} = +5$, $V_{GG} = -29$
Pulse Rise, fall time	t_{R1}, t_F	10	—	100	10	—	100	ns	

**Typical values are at $+25^{\circ}C$ and nominal voltages.


TIMING DIAGRAM



TYPICAL OUTPUT CHARACTERISTICS



TYPICAL SUPPLY CURRENT VS POWER SUPPLY VOLTAGE



ELEC. ALTERABLE
NON-VOLATILE MEMORY