





SMA ATTENUATOR 6 DB 18 GHZ 2W

PAGE 1/2 ISSUE 08-06-15E SERIES PART NUMBER R411806121





Scale 1:1



All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING (μm)		
Body	STAINLESS STEEL	PASSIVATED		
Male center contact	BERYLLIUM COPPER	GOLD 2 OVER NICKEL 2		
Female center contact	BERYLLIUM COPPER	GOLD 1.3 OVER NICKEL2		
Outer contact	-	-		
Insulator	PTFE			
Gasket	SILICONE RUBBER			
Substrate	ALUMINA			
Resistor	THIN FILM			
Others parts	-	-		



Technical Data Sheet

SMA ATTENUATOR 6 DB 18 GHZ 2W

PAGE 2/2	ISSUE 08-06-15E	SERIES ATTENUATOR	PART NUMBER R411806121

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 4	4 - 8	8 - 12.4	12.4 - 18
V.S.W.R (≤)	1.15	1.20	1.25	1.35
Deviation(±dB)	0.40	0.40	0.50	0.80

Operating Frequency Range	DC - 18	GHz
Impedance	50	Ω
Nominal Attenuation	6	dB
Peak power at 25°C (1µs, 1‰)	100	W
Average power at 25°C	2	W (Free Air Cooled)
		W (Conduction Cooled)


MECHANICAL CHARACTERISTICS

Connectors	SMA		Male Female	MIL-C 39012
Weight	4,7200	g		

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55 /+125 °C
Storage temperature range	-55 /+125 °C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS