


N ATTENUATOR 16 DB 18 GHZ 2W

R414.716.161Series: **ATTENUATOR**





Scale 1:1



All dimensions are in mm.



COMPONENTS	MATERIALS	PLATING(μm)
BODY MALE CENTER CONTACT FEMALE CENTER CONTACT OUTER CONTACT INSULATOR GASKET SUBSTRATE RESISTOR OTHERS PARTS	STAINLESS STEEL BERYLLIUM COPPER BERYLLIUM COPPER PTFE SILICONE RUBBER ALUMINA THIN FILM	PASSIVATED GOLD 1.2 OVER NICKEL 2 GOLD 1.2 OVER NICKEL 2

Issue: 0839 A

In the effort to improve our products, we reserve the right to make changes judged to be necessary.



N ATTENUATOR 16 DB 18 GHZ 2W

R414.716.161

Series: ATTENUATOR

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 4	4 - 8	8 - 12.4	12.4 - 18
V.S.W.R (≤)	1.15	1.20	1.25	1.35
Deviation(±dB)	0.60	0.60	0.60	0.60

DC - 18	GHz
50	Ω
16	dB
100	W
2	W (Free Air Cooled)
	W (Conduction Cooled)
	50 16


MECHANICAL CHARACTERISTICS

Connectors	N	Male Female	MIL-C 39012
Weight	60,0400 g		

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55 /+125 °C
Storage temperature range	-55 /+125 °C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS

