





N ATTENUATOR 6 DB 4 GHZ 30W

PAGE 1/2 ISSUE 20-12-18D SERIES PART NUMBER R417306130

## **SCALE 1:1**





All dimensions are in mm. Tolerances according ISO 2768 m-H



COMPONENTS	MATERIALS	PLATING (μm)
Body	STAINLESS STEEL	PASSIVATED
Male center contact	BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL PHOSPHORUS 2
Female center contact	BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL PHOSPHORUS 2
Outer contact		
Insulator	PTFE	
Gasket	SILICONE RUBBER	
Substrate	ALUMINA	
Resistor	THICK FILM	
Others parts	ALUMINIUM	BLACK ANODIZATION







PAGE 2/2 ISSUE 20-12-18D SERIES ATTENUATOR PART NUMBER R417306130

#### **ELECTRICAL CHARACTERISTICS**

Frequency (GHz)	DC - 1	1 - 2	2 - 4
V.S.W.R (≤)	1.10	1.20	1.35
Deviation(±dB)	0.60	0.60	0.60


DC - 4	GHz
50	Ω
6	dB
5000	W
	W (Free Air Cooled)
30	W (Conduction Cooled)
	50 6 5000


# MECHANICAL CHARACTERISTICS

Connectors	N	Male Female	MIL-C 39012
Weight	142.4800	q	

#### **ENVIRONMENTAL CHARACTERISTICS**

Operating temperature range	-55 /+125	°C
Storage temperature range	-55 /+125	°C





### **SPECIFICATION**

#### **OTHER CHARACTERISTICS**