





SMA ATTENUATOR 6 DB 2 GHZ 100W

PAGE 1/2 ISSUE 17-08-18B SERIES ATTENUATOR PART NUMBER R417806118





All dimensions are in mm. Tolerances according ISO 2768 m-H



COMPONENTS	MATERIALS	PLATING (μm)
Body Male center contact Female center contact	STAINLESS STEEL BERYLLIUM COPPER BERYLLIUM COPPER	PASSIVATED GOLD 0.5 OVER NICKEL PHOSPHORUS 2 GOLD 0.5 OVER NICKEL PHOSPHORUS 2
Outer contact		
Insulator	PTFE	
Gasket	SILICONE RUBBER	
Substrate	ALUMINA	
Resistor	THICK FILM	
Others parts	ALUMINIUM	BLACK PAINTING



# **Technical Data Sheet**

SMA ATTENUATOR 6 DB 2 GHZ 100W

PAGE <b>2/2</b>	ISSUE 17-08-18B	SERIES ATTENUATOR	PART NUMBER <b>R417806118</b>
-----------------	-----------------	----------------------	-------------------------------

### **ELECTRICAL CHARACTERISTICS**

Frequency (GHz)	DC - 1	1 - 2
V.S.W.R (≤)	1.10	1.25
Deviation(±dB)	1.0	1.0

DC - 2	GHz
50	Ω
6	dB
5000	W
100	W (Free Air Cooled)
	W (Conduction Cooled)
	50 6 5000


### MECHANICAL CHARACTERISTICS

Connectors	SMA	Male Female	MIL-C 39012
Weight	750,4300	g	

### **ENVIRONMENTAL CHARACTERISTICS**

Operating temperature range	<b>-55 /+125</b> °C
Storage temperature range	-55 /+125 °C

#### Power derating Versus temperature



## SPECIFICATION

#### **OTHER CHARACTERISTICS**