





SMA ATTENUATOR 10 DB 2 GHZ 80W

PAGE 1/2 ISSUE 17-08-18B SERIES ATTENUATOR PART NUMBER R417810118





All dimensions are in mm. Tolerances according ISO 2768 m-H



COMPONENTS	MATERIALS	PLATING (μm)	
Body Male center contact	STAINLESS STEEL BERYLLIUM COPPER	PASSIVATED GOLD 0.5 OVER NICKEL PHOSPHORUS 2	
Female center contact	BERYLLIUM COPPER	GOLD 0.5 OVER NICKEL PHOSPHORUS 2	
Outer contact	DTTT		
Insulator	PTFE		
Gasket	SILICONE RUBBER		
Substrate	ALUMINA		
Resistor	THICK FILM		
Others parts	ALUMINIUM	BLACK PAINTING	





SMA ATTENUATOR 10 DB 2 GHZ 80W

PAGE 2/2	ISSUE 17-08-18B	SERIES ATTENUATOR	PART NUMBER R417810118
-----------------	-----------------	----------------------	-------------------------------

ELECTRICAL CHARACTERISTICS

Frequency (GHz)	DC - 1	1 - 2
V.S.W.R (≤)	1.10	1.25
Deviation(±dB)	1.0	1.0

Operating Frequency Range	DC - 2	GHz
Impedance	50	Ω
Nominal Attenuation	10	dB
Peak power at 25°C (1µs, 1‰)	5000	W
Average power at 25°C	80	W (Free Air Cooled)
		W (Conduction Cooled)


MECHANICAL CHARACTERISTICS

Connectors	SMA	Male Female	MIL-C 39012
Weight	750,6900	g	

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range	-55 /+125	°C
Storage temperature range	-55 /+125	°C

Power derating Versus temperature



SPECIFICATION

OTHER CHARACTERISTICS